







RECOMMEND P.C.B LAYOUT
PCB TOLERANCE:±0.05 (TOP VIEW)



SPECIFICATIONS

Current Rating:1.0 Amps

Withstanding Voltage:AC 500V

Insulation Resistance:1000MΩ Min

Contact Resistance:20mΩ Max

Operation Temperature:−40° to+105°

Insrlator Material:Polyester(UL94V−0)

Contact Material:Brass

Standard:PA6T

Contact Plating:Gold Flash

Max.Processing Temp: 240°C for30−60seconds
(260°C for5seconds)

P/N	PIN	DIM.A	DIM.B
BX-PZ1.27-2-1PWZ	2*1	0.00	1.27
BX-PZ1.27-2-2PWZ	2*2	1.27	2.54
BX-PZ1.27-2-3PWZ	2*3	2.54	3.81
BX-PZ1.27-2-4PWZ	2*4	3.81	5.08
BX-PZ1.27-2-5PWZ	2*5	5.08	6.35
BX-PZ1.27-2-6PWZ	2*6	6.35	7.62
BX-PZ1.27-2-7PWZ	2*7	7.62	8.89
BX-PZ1.27-2-8PWZ	2*8	8.89	10.16
BX-PZ1.27-2-9PWZ	2*9	10.16	11.43
.....			
BX-PZ1.27-2-50PWZ	2*50	(PIN-1)x1.27	(PIN)x1.27

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	EMMA			料号 PART NO.	BX-PZ1.27-2-NPWZ			版本 REV.	A
			X.±0.30	X.*±5°	审核 CHECK	EVA			品名 TITLE	1.27PH H1.0 2mPin SMT W3.4 PCS.5 PAA.0 PBI.5 L7.2 6T			页次 SHEET	1/1
			.X±0.20	.X*±1°	核准 APPROVAL	JADE			客户料号 CUTM.NO.					
			.XX±0.10	.XX*±0.5°										
					单位 UNITS	MM	比例 SCALE	1:1						