




### SPECIFICATIONS

Current Rating: 1.5 Amps  
 Insulation Resistance: 1000M $\Omega$  Min  
 Contact Resistance: 20m $\Omega$  Max  
 Withstanding Voltage: AC 500V  
 Operation Temperature: -40° to +105°  
 Contact Material: Brass  
 Standard: PA6T  
 Insulator Material: Polyester (UL 94V-0)  
 Contact Plating: Gold Flash  
 Max. Processing Temp: 240°C for 30-60 seconds  
 (260°C for 5 seconds)



RECOMMEND P.C.B LAYOUT  
 PCB TOLERANCE:  $\pm 0.05$  (TOP VIEW)

P/N	PIN	DIM.A	DIM.B
BX-PZ2.0-2-1PUW	2*1	0.00	2.00
BX-PZ2.0-2-2PUW	2*2	2.00	4.00
BX-PZ2.0-2-3PUW	2*3	4.00	6.00
BX-PZ2.0-2-4PUW	2*4	6.00	8.00
BX-PZ2.0-2-5PUW	2*5	8.00	10.00
BX-PZ2.0-2-6PUW	2*6	10.00	12.00
BX-PZ2.0-2-7PUW	2*7	12.00	14.00
BX-PZ2.0-2-8PUW	2*8	14.00	16.00
BX-PZ2.0-2-9PUW	2*9	16.00	18.00
.....	.....	.....	.....
BX-PZ2.0-2-40PUW	2*40	(PIN-1)x2.0	(PIN)x2.0



制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	EMMA		料号 PART NO.	BX-PZ2.0-2-NPUW		版本 REV.	A
			X. $\pm 0.30$	X.* $\pm 5^\circ$	审核 CHECK	EVA		品名 TITLE	2.0PH H2.0 2xPin SMT PC6.5 PA3.8 PB2.5 L8.0 6T		页次 SHEET	1/1
			.X $\pm 0.25$	.X.* $\pm 1^\circ$	核准 APPROVAL	JADE		客户料号 CUTM.NO.				
			.XX $\pm 0.20$	.XX.* $\pm 0.5^\circ$	单位 UNITS	MM	比例 SCALE	1:1				