





RECOMMEND P.C.B LAYOUT
PCB TOLERANCE:±0.05 (TOP VIEW)



SPECIFICATIONS

Current Rating: 1.0 Amps
Withstanding Voltage: AC 500V
Insulation Resistance: 1000MΩ Min
Contact Resistance: 20mΩ Max
Operation Temperature: -40°to+105°
Insulator Material: Polyester(UL94V-0)
Contact Material: Brass
Standard: PA6T
Contact Plating: Gold Flash
Max.Processing Temp: 240°C for30-60seconds
(260°C for5seconds)

P/N	PIN	DIM.A	DIM.B
BX-PZ1.27-1-1PZZ	1	0.00	1.27
BX-PZ1.27-1-2PZZ	2	1.27	2.54
BX-PZ1.27-1-3PZZ	3	2.54	3.81
BX-PZ1.27-1-4PZZ	4	3.81	5.08
BX-PZ1.27-1-5PZZ	5	5.08	6.35
BX-PZ1.27-1-6PZZ	6	6.35	7.62
BX-PZ1.27-1-7PZZ	7	7.62	8.89
BX-PZ1.27-1-8PZZ	8	8.89	10.16
BX-PZ1.27-1-9PZZ	9	10.16	11.43
.....			
BX-PZ1.27-1-50PZZ	50	(PIN-1)x1.27	(PIN)x1.27

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	EMMA			料号 PART NO.	BX-PZ1.27-1-NPZZ		版本 REV.	A
			X.±0.30	X.*±5°	审核	EVA			品名 TITLE	1.27PH H1.0 1xnPin 180# W2.0 PC2.3 PA3.9 PB1.0 L7.2 6T 0.4#		页次 SHEET	1/1
					CHECK	JADE			客户料号 CUTM.NO.				
			.X±0.20	.X*±1°	核准 <th colspan="3"></th> <td></td> <td colspan="3"></td>								
			.XX±0.10	.XX*±0.5°	APPROVAL <th colspan="3"></th> <td></td> <td colspan="3"></td>								
					单位 UNITS	MM	比例 SCALE	1:1	 Bossie (博锡)				