

REV.	DESCRIPTION	ECN NO.	NAME	DATE


- SPECIFICATION:**
- Material:
 - HOUSING&MOLDING:LCP,UL94 V-0,BLACK
 - CONTACTS:COPPER ALLOY T=0.20mm
 - MIDDLE CLIP:SUS301-1/2H,T=0.15mm
 - SHELL:SUS, T=0.30mm
 - Mechanical:
 - 2.1.Mating force:5~20Nf Max.;
 - 2.2.Unmating force:6~20Nf Min.;
 - 2.3.Durability:10000 Cycles;
 - Electrical:
 - 3.1.Current Rating:3A Max.;
 - 3.2.Voltage Rating:20V Max.;
 - 3.3.Dielectric Withstanding voltage:100VAc;
 - 3.4.Contact resistance:40m Ohms Max.;
 - 3.5.Insulation Resistance:100M Ohms Min.;
 - Environmental:
 - 4.1.Operating temperature:-40°C~+85°C;
 - 4.2.Wetting Temperature:265±5°C,5±0.5s
 - PLATING SPECIFICATION:
 - 5.1.CONTACTS:
CONTACT AREA PLATED:Au G/F"
 - 5.2.FRONT SHELL&TOP SHELL:
Ni 30~50u".UNDER PLATED OVER ALL.

PIN	SIGNAL	PIN	SIGNAL
A12	GND	B1	GND
A11		B2	
A10		B3	
A9	VBUS	B4	VBUS
A8	SBU1	B5	CC2
A7	D-	B6	D+
A6	D+	B7	D-
A5	CC1	B8	SBU2
A4	VBUS	B9	VBUS
A3		B10	
A2		B11	
A1	GND	B12	GND

RECOMMENDED P.C.B. LAYOUT (T:1.0~1.2mm)
TOLERANCE UNSPECIFIED ±0.05mm



GENERAL TOLERANCE		DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD		
DIM. TOL. .x ±0.35 .xx ±0.25 .xxx ±0.15 GENERAL ANGLE: .X° ±3° .XX° ±2.5° .XXX° ±2.0°		TITLE: TYPE-C 16pin 母座 板上型 帶塑胶柱		
DWG. NO.: UC09-0B16F00P11		CHECKED: MAX		
PART NO.: UC09-0B16F00P11		DRAWN: ELLA		
UNIT: mm	SCALE: none	SHEET: 1 of 1	DWG. SIZE: A4 LAYER: bxconn	



REV.	DESCRIPTION	ECN NO.	NAME	DATE

- 说明:
1. 每卷前后各空 16PCS, 尾部用美纹纸封住;
 2. 将产品放满盘后, 再卷一圈保护带, 用美纹纸将其封住, 并贴上 1Pcs 物料标签;
 3. 每 10 卷盘一叠共 10000Pcs 并装入 1 个外箱内;
 4. 在搬运过程中要轻拿轻放;
 5. 在运输中不可堆放过多 (1.8M 最高), 不可重压;
 6. 跌落测试条件:
成品箱从 1.2 米高度自由落体 (一角三棱六面):
a. 产品不可跑出下带凹槽;
b. 产品不可有摔伤, 变形;
c. 内包装材料不可严重破损.

NO.	NAME	SPEC	Q'TY
①	TYPE C RECEPTACLE		10000PCS/CARTON
②	CARRIER TAPE	W=24mm,T=0.35mm	1000PCS/PLATE
③	COVER TAPE	W=21.5mm	10PLATES/CARTON
④	REEL PLATE	φ330*100*24.4mm	10PCS/CARTON
⑤	RoHS LABEL		10PCS/CARTON
⑥	PRODUCT LABER		10PCS/CARTON
⑦	CARTON	350*340*310mm	1PCS/PACKAGE

GENERAL TOLERANCE	DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD	
DIM. .x ±0.35 .xx ±0.25 .xxx ±0.15	TITLE: TYPE-C 16pin 母座 板上型 带塑胶柱	
GENERAL ANGLE: .X' ±3° .XX' ±2.5° .XXX' ±2.0°	DWG. NO.: UC09-0B16F00P11	CHECKED: MAX
	PART NO.: UC09-0B16F00P11	DRAWN: ELLA
UNIT: mm	SCALE: none	SHEET: 1 of 1
	DWG. SIZE: A4	LAYER: bxconn
	APPROVED: WILL	

