




GT-A2001 H F-1 XX X 01


G-Switch
Series No
Connector
 H-Housing
F-Female

Housing Colour
 W-White
Pin Q' PY
 02~12
Row NO
 1-Single Row




2pin

G-Switch Specification:
 1.Current rated: 2.0A AC/DC
 2.Voltage rating: 100V AC/DC
 3.Withstanding voltage: 800V AC
 4.Contact resistance: 10mΩ max.
 5.Insulation resistance: 1000MΩ min
 6.Durability cycle: 30Cycles
 7.Removal force: 1.20kgf/Pin min
 8.Operating temperature range: -25°C ~ +85°C



2pin



2pin



5pin

Ordering Information:

Circuit	Dimensions(mm)			Circuit	Dimensions(mm)		
	A	B	C		A	B	C
02	2.00	6.00	4.60	08	14.00	18.00	16.60
03	4.00	8.00	6.60	09	16.00	20.00	18.60
04	6.00	10.00	8.60	10	18.00	22.00	20.60
05	8.00	12.00	10.60	11	20.00	24.00	22.60
06	10.00	14.00	12.60	12	22.00	26.00	24.60
07	12.00	16.00	14.60	--	--	--	--

SCALE: 1:1 UNIT: mm
 SIZE: A4

Title: Housing 2.00mm Pitch PH Female
 Molde Code: GT-A2001HF-1XXX01

Unless otherwise General Tolerance:
 X ±0.40
 X.x ±0.30
 X.xx ±0.20
 X° ±5°
 X.x° ±3°

DRAWN	CHECKED	APPROVED	DATE
Hu	Chen	Chen	2021.10.18



1	HOUSING	PA66,94V-0	WHITE
NO.	PART NAME	MATERIAL	REMARK

