






REACH & RoHS
COMPLIANT

REV.	ECN / DESCRIPTION	BY	DATE
A0	NEW	X.YAN	2022.09.23



DETAIL "X"
SCALE 2:1



PC Board Layout Top View

NOTES:

MATERIAE

1. HOUSING MATERIAL: PBT, COLOR IS YELLOW , UL94V-0.
2. CONTACT MATERIAL: PHOSPHOR BRONZE 0.46mm.
3. PLATING: PLATING OVER NICKEL

ELECTRICAL:

1. VOLTAGE RATING: 125 VAC RMS.
2. CURRENT RATING: 1.5 AM
3. CONTACT RESISTANCE: 30 MILLIOHMS MAX.
4. INSULATION RESISTANCE: 500 MEGOHMS MIN @ 500V DC
5. DIELECTRIC WITHSTANDI RESISTANCE: 500V AC RMS 50HZ. 1MIN.

MECHANICAL:

1. DURRABILI : 750 CYCLES MIN.
2. PCB RETENTION PRE-SOLDER: 1 LB MIN.

ENVIRONMENT AL:

- 1 STORAGE: -40 ~+85
2. OPERATION -40 ~+85

PART NUMBER	COLOR
R1488R53B	BLACK
R1488R53Y	YELLOW
R1488R53G	GRAY

CND-tek
磁联达

深圳磁联达电子有限公司
Shenzhen magnetic Lianda Electronics Co., LTD

Address: 505, West Block, No. 221, Niucheng Road, Niucheng Village, Baiwang Community, Xili Street, Nanshan District, Shenzhen
E-mail: sales1@cd-tek.com 0755-27652992 29016433 Website:www.cd-tek.com

TITLE: 1*4 8P8C 53MINI 13.56	SIZE A4	UNITS MM[INCH]	GENERAL TOLERANCES UNLESS SPECIFIED		APPROVED BY: QG.CHEN
PART NO.: R1488R53Y	SACLE 1:1	REV A0	x±0.35	x°±3.0°	CHECKED BY: SL.WANG
REMARK:	SHEET 1/1		.xx±0.25	.xx°±1.5°	DESIGND BY: X.YAN
			.xxx±0.10	.xxx°±1.0°	