


Specification:

1. Rating : DC 5V 0.01A;
2. Resolution: 12 pulses/360° for each phase, 12 Detents 12 Pulse;
3. Insulation resistance:  $\geq 50M\Omega$  (50VDC).
4. Withstand voltage: 50VAC.
5. Rotational torque: 5-20gf.cm;
6. Life test: 100000cycles min.
7. Operation temperature range:  $-40^{\circ}C \sim 85^{\circ}C$ .
8. Preservative temperature range:  $-40^{\circ}C \sim 85^{\circ}C$ .

A-C

B-C



12pulse 12click



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X' ±2' X.X' ±0.5'	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: EC04全码 H=2.85mm编码器
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO. HVCW-EC04-285-X
UNIT: mm [inch] SCALE:1:1 SIZE: A4	APPROVED BY: 邱敏	DATE : 2014-02-23	MOLD NO.
			DRAW NO: HVC-2603131636
			SHEET NO. 1 OF 1