



NOTES:

备注

1. Brass or purple copper, Bright tin-plating  
黄铜或紫铜, 镀亮锡
2. Wire screw hole M5  
压线螺孔M5
3. Current Rating: 70A  
额定电流: 70A
4. There shall be no defects such as pin deformation and burrs.  
不得有脚变形, 毛刺等缺陷
5. Unmarked dimensions refer to tolerances  
未标注的尺寸参考公差



**Ordering Information**

HC - \* \*\* \* \* - \*\*\*\* - \* \*\* \* \* - 07

Type	Thickness	Screw Thread	Welding Feet	Series	9-01P	Product No.	Material
M5x1.1 Teeth (抽牙)	08-0.8mm	3*0.3 (螺牙)	1620±16x20mm	.....	FD-Flap	.....	默认Copper (黄铜)
M5x1.1 Nut (螺母)	10±1.0mm	4*0.4 (螺牙)	.....	.....	.....	.....	.....
M5x1.1 Gasket (垫片)	12±1.0mm	5*0.5 (螺牙)	.....	.....	.....	.....	.....
	15±1.5mm	5*0.5 (螺牙)	.....	.....	.....	.....	.....
	20±2.0mm	6*0.6 (螺牙)	.....	.....	.....	.....	.....
	25±2.5mm	6*0.6 (螺牙)	.....	.....	.....	.....	.....
	30±3.0mm	6*0.6 (螺牙)	.....	.....	.....	.....	.....
	32±3.2mm	.....	.....	.....	.....	.....	.....

			GENEAL TOLERANCE	制图	07	深圳市华灿天禄电子有限公司 ShenzhenhuaciantianluELECTRONICS CO.,LTD			
			DIM TOL	审核					
			5 or more ±0.35	批准		产品名称	PCB 焊接端子 厚度1.2 贴片 抽牙	版本	A
			2~5 ±0.25	APPROVAL		TITLE	M5 4焊脚 30x11.5x7.9mm	REV.	
			0~2 ±0.15	比例		产品料号	HC-M1254-3011-S527-07	单位	mm
			Angle ±3.0°	投影		PART NO.		页次	1/1
序号	变更内容	日期		投影		MATERIAL		SHEET	
No.	MODIFY CONTENT	MODIFY DATE		Projection					