








NOTES:

- Material:  
Insulation:LCP,UL94V-0(Beige)  
Pin:Phosphor Bronze/Tin-Plated  
Tab:Phosphor Bronze/Tin-Plated
- Current Rating: 1A AC,DC
- Voltage Rating: 150V AC,DC
- Temperature Rang: -25°C~+85°C
- Contact Resistance: 20mΩ Max
- Insulation Resistance: 500MΩ Min
- Withstanding Voltage: 500V AC/minute



P.C.B Layout

Poles	DIM(mm)				
	A	B	C	D	E
3	2.50	8.65	7.25	5.25	3.0
4	3.75	9.90	8.50	5.5	3.0
5	5.00	11.15	9.75	6.75	3.5
6	6.25	12.40	11.00	8.0	3.5
7	7.50	13.65	12.25	9.25	4.0
8	8.75	14.90	13.50	10.5	4.3
9	10.00	16.15	14.75	11.75	4.3
10	11.25	17.40	16.00	13.0	4.3
11	12.50	18.65	17.25	14.25	4.3
12	13.75	19.90	18.50	15.5	4.3
13	15.00	21.15	19.75	16.75	7.2
14	16.25	22.40	21.00	18.0	7.2
15	17.50	23.65	22.25	19.25	7.2
16	18.75	24.90	23.50	20.5	7.2
17	20.00	26.15	24.75	21.75	7.2
18	21.25	27.40	26.00	23.0	7.2
19	22.50	28.65	27.25	24.25	7.2
20	23.75	29.90	28.50	25.5	7.2

CUSTOMER



深圳市臺華達科技有限公司  
SHENZHENSHI THD TECHNOLOGY CO., LTD.

GENERAL TOLERANCE  
UNLESS  
OTHERWISE SPECIFIED

DRAWN: **Kavin** 2018.06.28

CHECKED: **胡文** 2018.06.28

APPROVED: **黄德进** 2018.06.28

PART NO.  
THD12507-xxWR-SN

X.X ±0.20  
X.XX ±0.15  
X.XXX ±0.10  
ANG. ±2°

SHEET: 1/1

TITLE: WIRE TO BOARD, PLUG,  
PITCH 1.25mm, CRIMP TYPE,  
ASSEMBLY

UNIT: mm SCALE: 1:1 SIZE: A4 REV: X1

REV.	REVISIONS	CHK	DATE