



NOTES:

备注

- Copper, nickel base, matte tin
黄铜H62, 镍底, 镀雾锡
- Wire screw hole M4
压线螺孔M4
- Current Rating: 50A
额定电流: 50A
- Operating temperature: -40°C ~ +125°C
工作温度: -40°C ~ +125°C
- There shall be no defects such as pin deformation and burrs.
不得有脚变形, 毛刺等缺陷
- Unmarked dimensions refer to tolerances
未标注的尺寸参考公差

Ordering Information

HC - * ** * * - ***** - D *** * - 02

Type	Thickness	Screw Thread	Welding Feet	Series	DIP	Product No.	Material
M=11 Teeth (铆钉)	0.8mm	M4	0.8mm	0808/13.5mm	SMT	产品序号	HC=H62 Copper (黄铜)
N=Nut (螺母)	1.2mm	M4	1.2mm	150/10.2mm	Dip		HC=H62 Copper (黄铜)
G=Gasket (铆垫片)	1.2mm	M4	1.2mm			

			GENREL TOLERANCE	制图	02	深圳市华灿天禄电子有限公司 ShenzhenhuacantianlueELECTRONICS CO., LTD			
			DIM TOL	审核					
			5 or more ±0.35	批准		产品名称	PCB 焊接端子 厚度0.8 插板	版本	A
1	初版发行		2~5 ±0.25	比例		TITLE	铆垫片 M4 4焊脚 8x8x13.5mm	REV.	
序号	变更内容	日期	0~2 ±0.15	投影		产品料号	HC-RG0844-0808-D054-02	单位	mm
No.	MODIFY CONTENT	MODIFY DATE	Angle ±3.0°			PART NO.		页次	1/1
						MATERIAL		SHEET	