




NOTES:
备注

1. Brass or purple copper, Bright tin-plating
黄铜或者紫铜, 镀亮锡
2. Wire screw hole M5
压线螺孔M5
3. Current Rating: 黄铜 80A/紫铜 100A
额定电流: 黄铜 80A/紫铜 100A
4. There shall be no defects such as pin deformation and burrs.
不得有脚变形, 毛刺等缺陷
5. Unmarked dimensions refer to tolerances
未标注的尺寸参考公差



Ordering Information							
HC - * ** * * - * * * * - * * * * * - 07							
Type	Thickness	Screw Thread	Welding Feet	Series	Q-IMP	Product No.	Material
M-Hull Tooth (铆字)	08-0.8mm	2-6 (螺字)	0808-88mm	0808-88mm	S-SMT	产品序号	默认-Copper (铜)
Riv-Nut Nut (铆螺母)	12-1.2mm	4-8 (螺字)	2-2个	1020-1620mm	FB-Flag		PC-Red Copper (紫铜)
Riv-Rivet Gasket (铆垫片)	20-2.0mm	6-8 (螺字)	6-6个	Flag		
	25-2.0mm		8-8个				
	30-3.0mm						
	32-3.2mm						

			GENERL TOLERANCE	制图	07	深圳市华灿天禄电子有限公司 ShenzhenhuaciantianluELECTRONICS CO.,LTD			
			DIM TOL	审核		产品名称	PCB 焊接端子 厚度1.5 插板 铆垫片	版本	A
			5 or more ±0.35	批准		TITLE	紫铜 M5 4焊脚 12x12x10.5mm	REV.	
			2~5 ±0.25	APPROVAL		产品料号	HC-RG1554-1212-D701RC-07	单位	mm
			0~2 ±0.15	比例		PART NO.		页次	1/1
1	初版发行		Angle ±3.0°	投影		材料		SHEET	
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE				MATERIAL			