




NOTES:

- 备注
1. Copper, Bright tin plated  
黄铜, 镀亮镍
  2. Wire screw hole M4  
压线螺孔M4
  3. Current Rating: 45A  
额定电流:45A
  4. There shall be no defects such as pin deformation and burrs.  
不得有脚变形, 毛刺等缺陷
  5. Unmarked dimensions refer to tolerances  
未标注的尺寸参考公差



**Ordering Information**

HC - \* \*\* \* - \*\*\*\* - \* \*\* \* - 07

Type	Thickness	Screw	Welding	Series	Pin/P	Product No.	Material
Weld 1 Tooth (铆牙)	0.8±0.05mm	M4 (螺牙)	0808 (焊脚)	1620=16x20mm	Pin	产品序号	黄铜
Weld Nut (铆螺母)	1.0±0.05mm	M4 (螺牙)	22 (焊脚)	.....	Pin		镀亮铜
Weld Gasket (铆垫片)	1.5±0.05mm	M4 (螺牙)	4 (焊脚)		Dip		
	2.0±0.05mm		6 (焊脚)				
	2.5±0.05mm		8 (焊脚)				
	3.0±0.05mm						

		GENERAL TOLERANCE	制图	07	深圳市华灿天禄电子有限公司 ShenzhenhuacantianlueELECTRONICS CO.,LTD		
		DIM TOL	审核				
		5 or more ±0.35	批准		产品名称	PCB 焊接端子 厚度0.8 插板 铆垫片	版本
		2~5 ±0.25	比例		TITLE	M4 4焊脚 8x8x11.2mm	REV.
		0~2 ±0.15	投影		产品料号	HC-RG0844-0808-D204-07	单位
序号	变更内容	日期	投影		MATERIAL		页次
No.	MODIFY CONTENT	MODIFY DATE					SHEET
							1/1