




1. 材质和电镀:
 - 1.1 端子: 不锈钢 $T=0.10\text{mm}$, 弹片和焊脚刷金G/F
 - 1.2 塑胶: LCP UL94V-0
2. 正向应力: 30gf MIN, 10000次以上
3. 电气性能:
 - 3.1 额定电流: 1A MAX
 - 3.2 额定电压: 12V AC (RMS)
 - 3.3 耐电压: 100V AC FOR 1 MINUTE
 - 3.4 绝缘阻抗: 100 MEGAOHMS MIN
 - 3.5 接触阻抗: 50 MILLIOHMS MAX

P.C.BLAYEOUT
TOLERANCE: ± 0.05

 深圳市华宇创精密电子有限公司			
TOLERANCE: X.X ± 0.30 X.XX ± 0.25 X.XXX ± 0.15 X.' $\pm 2'$ X.X' $\pm 0.5'$	DRAWN BY :	DATE :	PART NAME:
	陈一鸣	2014-02-23	电池弹片 2PIN 4.7H 中心柱
  UNIT: mm [inch]	CHECKED BY:	DATE :	PART NO.
	马跃	2014-02-23	HWCW-TXT682547B
SCALE: 1:1 SIZE: A4	APPROVED BY:	DATE :	DRAW NO:
	邱敏	2014-02-23	HVC-2603131115
			SHEET NO.
			1 OF 1