


P.C.B LAYOUT TOP VIEW

Main technical performance	
Rated electrical load	30V 0.2A
Contact resistance	≤0.03Ω
Insulation resistance	≥100MΩ
Pressure resistance	AC 2.5V(50Hz)min
Insertion force	5~15N
Operating temperature range	-20C°~+70C°
service life	5000cycles



SCHEMATIC

MANUFACTURE DWG		东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd	
UNLESS OTHERWISE SPECIFIED TOLERANCES		TITLE: DC SOCKET	
DECIMALS:	ANGLES:	PAR	DC-031-A100
0~10 ±0.10		DWN	Lucas
10~20 ±0.15		CHKD	Ethan
20~50 ±0.20		APVD	Jacob
CUSTOMER COPY		SCALE:1:1	UNIT:MM
		SIZE:A4	SHEET:1F1
			REV:A