




### SPECIFICATIONS

Current Rating: 1.5 Amps  
 Insulation Resistance: 1000M $\Omega$  Min  
 Contact Resistance: 20m $\Omega$  Max  
 Withstanding Voltage: AC 500V  
 Operation Temperature: -40°to+105°  
 Contact Material: Brass  
 Standard: PA6T  
 Insulator Material: Polyester(UL 94V-0)  
 Contact Plating: Gold Flash  
 Max.Processing Temp: 240°C for30-60seconds  
 (260°C for 5 seconds)



RECOMMEND P.C.B LAYOUT  
 PCB TOLERANCE:±0.05 (TOP VIEW)



P/N	PIN	DIM.A	DIM.B
BX-PM2.0-01-NPY	1	0.00	2.00
BX-PM2.0-02-NPY	2	2.00	4.00
BX-PM2.0-03-NPY	3	4.00	6.00
BX-PM2.0-04-NPY	4	6.00	8.00
BX-PM2.0-05-NPY	5	8.00	10.00
BX-PM2.0-06-NPY	6	10.00	12.00
BX-PM2.0-07-NPY	7	12.00	14.00
BX-PM2.0-08-NPY	8	14.00	16.00
BX-PM2.0-09-NPY	9	16.00	18.00
.....	.....	.....	.....
BX-PM2.0-40-NPY	40	(PIN-1)x2.0	(PIN)x2.0

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	EMMA		料号 PART NO.	版本 REV.	A	
			X.±0.30	X.*±5°	审核 CHECK	EVA		品名 TITLE	2.0FH H6.35 1xnPin 180度 Y型 PC2.8 6T	页次 SHEET	1/1
			.X±0.20	.X*±1°	核准 APPROVAL	JADE		客户料号 CUTM.NO.			
			.XX±0.10	.XX*±0.5°	单位 UNITS	MM	比例 SCALE	1:1			

