



NOTES:

备注

1. Copper, nickel base, matte tin
黄铜H62, 镍底, 镀雾锡
2. Wire screw hole M4
压线螺孔M4
3. Current Rating: 45A
额定电流: 45A
4. Operating temperature: -40°C ~ +125°C
工作温度: -40°C ~ +125°C
5. There shall be no defects such as pin deformation and burrs.
不得有脚变形, 毛刺等缺陷
6. Unmarked dimensions refer to tolerances
未标注的尺寸参考公差



Ordering Information

HC - * ** * * - **** - D *** * - 02

Type	Thickness	Screw Thread	Welding Feet	Series	D-DIP	Product No.	Material
M=Full Teeth (抽牙)	08-0.8mm	3=M3 (螺牙)	3=脚	0808-8x8mm	S=SMT	产品序号	默认=Copper (黄铜)
RW=Rivet Nut (铆螺母)	10-1.0mm	4=M4 (螺牙)	4=脚	1620-16x20mm	FD=Flag Dip		RC=Red Copper (紫铜)
RG=Rivet Gasket (铆垫片)	12-1.2mm	5=M5 (螺牙)	2=2个			
	15-1.5mm	6=M6 (螺牙)	4=4个				
	20-2.0mm		6=6个				
	25-2.5mm		8=8个				
	30-3.0mm					
	32-3.2mm						

			GENEAL TOLERANCE	制图 DRAWING	02	深圳市华灿天禄电子有限公司 ShenzhenhuaciantianluELECTRONICS CO.,LTD			
			DIM TOL	审核 CHECK		产品名称 TITLE	PCB 焊接端子 厚度0.8 插板 铆垫片 M4 4焊脚 8x8x9.7mm	版本 REV.	A
			5 or more ±0.35	批准 APPROVAL		产品料号 PART NO.	HC-RG0844-0808-D053-02	单位 UNITS	mm
1	初版发行		2~5 ±0.25	比例 SCALE		材料 MATERIAL		页次 SHEET	1/1
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	0~2 ±0.15	投影 Projection					
			Angle ±3.0°						