


P.C.BLAYEOUT  
TOLERANCE:±0.05

1. 材质和电镀:
  - 1.1 端子: 不锈钢T=0.10mm, 弹片和焊脚刷金G/F
  - 1.2 塑胶: LCP UL94V-0
2. 正向应力:30gf MIN, 10000次以上
3. 电气性能:
  - 3.1 额定电流:1A MAX
  - 3.2 额定电压: 12V AC (RMS)
  - 3.3 耐电压:100 V AC FOR 1 MINUTE
  - 3.4 绝缘阻抗 :100 MEGAOHMS MIN
  - 3.5 接触阻抗: 50 MILLIOHMS MAX

 <b>深圳市华宇创精密电子有限公司</b>			
TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X' ±2' X.X' ±0.5'	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: 电池弹片 2PIN 4.3H 中心柱
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO. HYCW-TXT682543B
UNIT: mm [inch] SCALE:1:1 SIZE: A4	APPROVED BY: 邱敏	DATE : 2014-02-23	DRAW NO: HYC-2603131029
			SHEET NO. 1 OF 1