



说明:

1. 特性:

- 额定电压 :500V AC MIN
- 小针额定电流:5A
- 大针额定电流:10A, 20A, 30A, 40A
- 接触阻抗 :30m Ω MAX.
- 绝缘阻抗 :3000M Ω MIN. at 500V DC
- 耐电压值 :1000V AC RMS for 1Minute
- 温度范围 : -55 $^{\circ}$ C~+105 $^{\circ}$ C
- 盐雾时间 : 48H

2. 材料:

- 胶芯 : PBT, rated UL94V-0
- 接触点: 铜合金, 镀金1u"-30u"
- 铁壳 : SPCC, 前壳电镀后壳镀锡

额定电流	ϕA	ϕB	适用线径
10A	$\phi 2.60$	$\phi 1.80$	14~16AWG
20A	$\phi 3.60$	$\phi 2.80$	10~12AWG
30A	$\phi 4.50$	$\phi 3.50$	8~10AWG
40A	$\phi 5.40$	$\phi 4.60$	6~8AWG

TOLERANCE TABLE

.0	± 0.30
.00	± 0.20
.000	± 0.05

APPROVED:	DATE:	Ckmtw 深圳市灿科盟实业有限公司 CHANKEMENG INDUSTRY CO., LTD			
CHECKED:	DATE:	TITLE: DW-5W1M 公头 焊线式 长针 全金 光孔			
DRAWN: HCY	DATE: 2024-04-21	PART. NO.	D-DW0005PM-A000		
		UNIT	mm	SCALE	free
		FILE NO.	Ckmtw-DW-00010	REV.	A