




CIRCUIT DIAGRAM



P. C. B SOLDER LAND DIMENSION

主要技术参数、性能

The Main Thchnology Performance

额定电流、电压 Rate voltage,current	50mA DC12V
接触电阻 Contact resistance	$\leq 100\text{m}\Omega$
按力 Operating force	$\pm 50\text{gf}$
行程 Travel	$0.25 \pm 0.10\text{mm}$
绝缘电阻 Insulated resistance	$\geq 100\text{M}\Omega$
介电强度 Dielectric strength	$\geq 250\text{VAC}/1\text{mi}$


E	手柄	PPS	见规格
D	盖板	黄铜	镀铜锡
C	弹片	覆银铜	单面镀银
B	基座	PPS	见规格
A	卡件	黄铜	镀银
序号	名称	材质	颜色/镀涂

J	4	B	73	1	1	1	0
<u> </u>	<u> </u>	<u> </u>	<u> </u>	<u> </u>	<u> </u>	<u> </u>	<u> </u>
(A)	(B)	(C)	(D)	(E)	(F)	(G)	(H)

A. 系列:J-6*6mm
B. 贴装方式:4-立式贴片
C. 引脚规格:B-4PIN
D. 操作高度:73-7.3mm
E. 操作力度:1-160gf
F. 操作寿命:1-100,000次
G. 固定方式:1-无柱
H. 物料编码:1-长脚距

			GENERAL TOLERANCE	
			$\geq 0-2 <$	$+0.15$
DESIGN	WANGGUIFA	2018.06.12	$\geq 2-5 <$	± 0.25
CHECKED	ZHENGUILAN	2018.06.12	$\geq 0-2 <$	± 0.15
APPROVED	LILIANJIANG	2018.06.14	≥ 5	± 0.35

FIRST VIEW



The copyright belongs to samzo parts [China] Co., Ltd. please use the material after samzo parts agree to authorize. The final right of interpretation belongs to samzo parts.
WWW.KKK-JP.COM

TITLE:	
--------	--

6*6*7.3方头立式贴片长脚距

of DWG NO: J4B-P30179

PART NO: J4B7318020

MODEL NO: J4B731111

NAME:

TACT SWITCH

SAMZO COMPONENTS
Electronic switch and connector manufacturer