



技术要求Specification:

1. 材质Material: PA66 UL94V-0:
2. 额定电流 Current rating:1.0A AC,DC
3. 额定电压 Voltage rating:50V AC,DC
4. 温度范围 Temperature range:-25℃to+85℃
5. 接触电阻 Contact resistance:≤20mΩ
6. 绝缘电阻Insulation resistance:≥100MΩ
7. 耐压Withstand voltage:250V AC/minute
8. 塑件表面平整光洁, 无明显的毛刺、气泡、变形、浇口拉伤、缺料等不良现象。

Plastic surface smooth and clean, no obvious burrsbubbles, distortion, gate strain, lack of material and otherundesirable phenomena.

Part No	Pin	A	B	C
BX-MX1.25-2PJK	2	1.25	4.30	3.00
BX-MX1.25-3PJK	3	2.50	5.55	4.25
BX-MX1.25-4PJK	4	3.75	6.80	5.50
BX-MX1.25-5PJK	5	5.00	8.05	6.75
BX-MX1.25-6PJK	6	6.25	9.30	8.00
BX-MX1.25-7PJK	7	7.50	10.55	9.25
BX-MX1.25-8PJK	8	8.75	11.80	10.50
BX-MX1.25-9PJK	9	10.00	13.05	11.75
BX-MX1.25-10PJK	10	11.25	14.30	13.00
BX-MX1.25-11PJK	11	12.50	15.55	14.25
BX-MX1.25-12PJK	12	13.75	16.80	15.50
BX-MX1.25-13PJK	13	15.00	18.05	16.75
BX-MX1.25-14PJK	14	16.25	19.30	18.00
BX-MX1.25-15PJK	15	17.50	20.55	19.25
BX-MX1.25-16PJK	16	18.75	21.80	20.50

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	EMMA		料号 PART NO.	BX-MX1.25-NPJK		版本 REV.	A
			X.±0.30	X.*±1*	审核 CHECK	EVA		品名 TITLE	MX1.25MM HOUSING		页次 SHEET	1/1
			.X±0.20		核准 APPROVAL	JADE		客户料号 CUTM.NO.				
			.XX±0.10		单位 UNITS	MM	比例 SCALE	1:1	Bossie (博锡)			