


Part No	PIN	A	B	C
BX-MX1.25-2PCB	2	1.25	7.65	3.05
BX-MX1.25-3PCB	3	2.50	8.90	4.30
BX-MX1.25-4PCB	4	3.75	10.15	5.55
BX-MX1.25-5PCB	5	5.00	11.40	6.80
BX-MX1.25-6PCB	6	6.25	12.65	8.05
BX-MX1.25-7PCB	7	7.50	13.90	9.30
BX-MX1.25-8PCB	8	8.75	15.15	10.55
BX-MX1.25-9PCB	9	10.00	16.40	11.80
BX-MX1.25-10PCB	10	11.25	17.65	13.05
BX-MX1.25-11PCB	11	12.50	18.90	14.30
BX-MX1.25-12PCB	12	13.75	20.15	15.55
BX-MX1.25-13PCB	13	15.00	21.40	16.80
BX-MX1.25-14PCB	14	16.25	22.65	18.05
BX-MX1.25-15PCB	15	17.50	23.90	19.30
BX-MX1.25-16PCB	16	18.75	25.15	20.55

- NOTES:  
 1.BASE: PA6T  
 2.PIN: Brass  
 3.Solder Tab: Brass

- SPECIFICATIONS:  
 1.Spacing: 1.25  
 2.Voltage Rating: 125V AC DC  
 3.Current Rating: 1A AC DC  
 4.Insulation Resistance: 100MΩ Min  
 5.Contact Resistance: 20mΩ Max  
 6.Withstanding voltage: 500V AC 1/Minute  
 7.Temperatuer Range: -25℃ ~+ 85℃



制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	EMMA		料号 PART NO.	BX-MX1.25-NPCB		版本 REV.	A
			X.±0.20	X'.:±5°	审核 CHECK	EVA		品名 TITLE	WAFER 1.25 超薄		页次 SHEET	1/1
			.X±0.10	X.X':±3°	核准 APPROVAL	JADE		客户料号 CUTM.NO.				
			.XX±0.05	X.XX':±1°	单位 UNITS	MM	比例 SCALE	1:1				