

NOTES: SPECIFICATION

1. MATERIAL:
   HOUSING: THERMOPLASTIC, HIGH TEMP, UL94V-0, BLACK COLOR,
   CONTACTS: COPPER ALLOY.
   PEGS: COPPER ALLOY.

2. FINISH:
   CONTACTS: SELECTED GOLD PLATING ON THE CONTACT AREA,
   1u" MIN. GOLD PLATING ON THE SOLDERTAILS,
   50 u" MIN. NICKEL UNDERPLATING OVER ALL.
   PEGS: 120u" MIN. MATTE-TIN OVER 50u" MIN. NICKEL.

CURRENT RATING : 0.5A 50V AC/DC
CONTACT RESISTANCE : 55 mΩ MAX
INSULATION RESISTANCE : 500 MΩ MIN AT 500V DC
OPERATING TEMPERATURE : -55°C~80°C









RECOMMENDED P.C.BOARD PATTERN LAYOUT

制图 DRAWN	文件标准 DESCRIPTION	日期 DATE	GENERL TOLERANCE		制图 DRAWING	EMMA	料号 PART NO.	BX-JSZ0.8-5.6H52P	版本 REV.	A
			X.±0.30	X.°±5°	审核 CHECK	EVA	品名 TITLE	0.80MM PITCH MINPCIEXPRESS HIGH=5.6mm 52 PIN CONNECTOR	页次 SHEET	1/1
			.X±0.25	.X°±1°	核准 APPROVAL	JADE	客户料号 CUTM.NO.			
			.XX±0.15		单位 UNITS	MM	比例 SCALE	1:1		

Bossie（博锡）