



	02-10P	0.10	MAX
	11P-16P	0.12	MAX



Part No	Pin	A	B	C	D
BX-HY2.0-2PLT	2	2.00	8.00	2.50	4.90
BX-HY2.0-3PLT	3	4.00	10.00	2.50	6.90
BX-HY2.0-4PLT	4	6.00	12.00	5.00	8.90
BX-HY2.0-5PLT	5	8.00	14.00	7.00	10.90
BX-HY2.0-6PLT	6	10.00	16.00	9.00	12.90
BX-HY2.0-7PLT	7	12.00	18.00	11.00	14.90
BX-HY2.0-8PLT	8	14.00	20.00	13.00	16.90
BX-HY2.0-9PLT	9	16.00	22.00	15.00	18.90
BX-HY2.0-10PLT	10	18.00	24.00	17.00	20.90
BX-HY2.0-11PLT	11	20.00	26.00	19.00	22.90
BX-HY2.0-12PLT	12	22.00	28.00	21.00	24.90
BX-HY2.0-13PLT	13	24.00	30.00	23.00	26.90
BX-HY2.0-14PLT	14	26.00	32.00	25.00	28.90
BX-HY2.0-15PLT	15	28.00	34.00	27.00	30.90
BX-HY2.0-16PLT	16	30.00	36.00	29.00	32.90

NOTES:

- 1.BASE: LCP
- 2.PIN: Brass
- 3.Solder Tab: Brass

SPECIFICATIONS:

- 1.Spacing: 2.0
- 2.Voltage Rating: 250V AC DC
- 3.Current Rating: 2A AC DC
- 4.Insulation Resistance: 800MΩ Min
- 5.Contact Resistance: 20mΩ Max
- 6.Withstanding voltage: 500V AC 1/Minute
- 7.Temperatuer Range: -25℃ ~+ 85℃

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	EMMA	料号 PART NO.	BX-HY2.0-NPLT	版本 REV.	A										
			X.±0.20	X'.:±5°							审核 CHECK	EVA	品名 TITLE	WAFER 2.00 立脚带扣	页次 SHEET	1/1				
			.X±0.10	X.X':±3°													核准 APPROVAL	JADE	客户料号 CUTM.NO.	
			.XX±0.05	X.XX':±1°																
						Bossie (博锡)														