



Technical Index

1. Temperature range: $-20^{\circ}\text{C} \sim 85^{\circ}\text{C}$.
2. Rated voltage: 30V AC/DC.
3. Rated current: 0.5A AC/DC.
4. Contact resistance: $\leq 20\text{m}\Omega$.
5. Dielectric withstanding voltage: 200V AC/minute.
6. Insulation resistance: $\geq 100\text{M}\Omega$.
7. Apply to gauge: AWG#28~#32 (O.D 0.6mm MAX).

序号	品名	材质
1	端子	Phosphor Bronze Bright tin plated

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	EMMA		料号 PART NO.	BX-0.8-DZ		版本 REV.	A
			X.±0.30	X.*±5°	审核 CHECK	EVA		品名 TITLE	0.80 Pitch C型WTB公共端子		页次 SHEET	1/1
			.X±0.25	.X*±1°	核准 APPROVAL	JADE		客户料号 CUTM.NO.				
			.XX±0.15		单位 UNITS	MM	比例 SCALE	1:1	Bossie (博锡)			