








RECOMMENDED PCB LAYOUT
GENERAL TOLERANCE ±0.05

Specifications:

Electrical:

- 1.Current Rating
1.5A/contact terminal
- 2.Voltage Rating
30V DC
- 3.Contact Resistance
30 milliohms MAX
- 4.Dielectric Withstanding Voitage:
500 V AC AT Sea Level
- 5.Lnsulation Resistance:
1000MEGA ohms MIN

Mechanical:


- 1.Cnnector Mate and Unmate Force
Mate force:3.75kgf(MAX)
Unmate force:1.02kgf(MIN)
- 2.Terminal Retention
1.2kgf(MIN)

Material:

- 1.Housing:
Hing Temperature Tnermaplastics,
UI 94V-0 PBT White
- 2.Contact:Copper Alloy C2680
- 3.Shell: Copper Alloy C2680/SPCC

Finish:

- 1.Contact: Plated Gold in Mating Area;
Tin On Solder Talls.
- 2.Shell:
Nickel Plating

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	EMMA			料号 PART NO.	BX-TYPE-B-MWC6P		版本 REV.	A
			X.±0.30	X.*±3°	审核 CHECK	EVA			品名 TITLE	USB B/F 90°DIP(弯脚)		页次 SHEET	1/1
			.X±0.20	.X*±2°	核准 APPROVAL	JADE			客户料号 CUTM.NO.				
			.XX±0.10		单位 UNITS	MM	比例 SCALE	1:1	 Bossie (博锡)				