









PAD AREA

KEEP OUT AREA

RECOMMENDED PCB LAYOUT

GENERAL TOLERANCE ± 0.05

MicroSD Card

NOTES:

1. MATERIAL:

INSULATOR: HIGH TEMPERATURE THERMO PLASTIC

FLAMMABILITY RATING: UL94V-0 COLOR: BLACK

CONTACT: COPPER ALLOYS


COVER: STAINLESS STEEL

2. CONTACT AREA PLATING: GOLD OVER NI

3. SOLDER TAIL COPLANARITY MUST BE WITHIN 0.10MAX.


TF CARD PIN DEFINE

PIN NO.	NAME	TYPE	DESCRIPTION
1	DAT2	I/O/PP	DATE LINE(BIT2)
2	CD/DAT3	I/O/PP	CARD DETECT DATE LIN(BIT3)
3	CMD	PP	COMMAND RESPONSE
4	VDD	S	SUPPLY VOLTAGE
5	CLX	I	CLOCK
6	VSS	S	SUPPLY VOLTAGE GROUND
7	DAT0	I/O/PP	DATE LINE(BIT0)
8	DAT1	I/O/PP	DATE LINE(DIT1)





制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE	制图 DRAWING	EMMA	料号 PART NO.	BX-TF-1.9HJ	版本 REV.	A
			X.±0.30	X.±2°	审核 CHECK	品名 TITLE	T-FLASH CARD HINGED 读卡卡	页次 SHEET	1/1
			.X±0.20	.X°±1°	核准 APPROVAL	客户料号 CUTM.NO.			
			.XX±0.10		单位 UNITS	比例 SCALE	1:1		
					MM				

Bossie (博锡)




客户拉出方向

自粘上贴



4个护角

95*95*290 K3K




NOTES

1. NUMBER OF CONNECTORS: 1000PCS/REEL
2. LEAD TAPE LENGTH

EMPTY 10PCS MIN		PART 1000PCS		EMPTY 10PCS MIN	COVER TAPE (300mm Min)
LEADER 300mm MIN		COMPONENT SUPPLIER		TRAILER 300mm MIN	

3. QUANTITY: 10000PCS/CARTON

上下各1PCS 珍珠棉





LABEL


胶纸工字型封箱

CARTON

350*350*340 K=K



10 Reels

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	EMMA		料号 PART NO.	BX-TF-1.9HJ		版本 REV.	A		
			X.±0.30	X.°±2°	审核 CHECK	EVA		品名 TITLE	T-FLASH CARD HINGED 翻盖卡		页次 SHEET	1/1		
			.X±0.20	.X°±1°	核准 APPROVAL	JADE		客户料号 CUTM.NO.						
			.XX±0.10		单位 UNITS	MM	比例 SCALE	1:1					 Bossie (博锡)	