




SPECIFICATIONS

Current Rating: 3Amps  
 Insulation Resistance: 1000MΩ Min  
 Contact Resistance: 20mΩ Max  
 Withstanding Voltage: AC 1000V  
 Operation Temperature: -40° to +105°  
 Contact Material: Brass  
 Insulator Material: Polyester (UL 94V-0)  
 Contact plating: Gold Flash  
 Standard: PA6T  
 Max. Processing Temp: 240°C for 30-60 seconds  
 (260°C for 10 seconds)

P/N	PIN	DIM.A	DIM.B
BX-IDC2.54-2-3PWZ	2*3	5.08	7.62
BX-IDC2.54-2-4PWZ	2*4	7.62	10.16
BX-IDC2.54-2-5PWZ	2*5	10.16	12.70
BX-IDC2.54-2-6PWZ	2*6	12.70	15.24
BX-IDC2.54-2-7PWZ	2*7	15.24	17.78
BX-IDC2.54-2-8PWZ	2*8	17.78	20.32
BX-IDC2.54-2-9PWZ	2*9	20.32	22.86
BX-IDC2.54-2-10PWZ	2*10	22.86	25.40
BX-IDC2.54-2-12PWZ	2*12	27.94	30.48
BX-IDC2.54-2-13PWZ	2*13	30.48	33.02
BX-IDC2.54-2-14PWZ	2*14	33.02	35.56
BX-IDC2.54-2-15PWZ	2*15	35.56	38.10
BX-IDC2.54-2-16PWZ	2*16	38.10	40.64
BX-IDC2.54-2-17PWZ	2*17	40.64	43.18
BX-IDC2.54-2-18PWZ	2*18	43.18	45.72
BX-IDC2.54-2-20PWZ	2*20	48.26	50.80
BX-IDC2.54-2-22PWZ	2*22	53.34	55.88
BX-IDC2.54-2-25PWZ	2*25	60.96	63.50
BX-IDC2.54-2-30PWZ	2*30	73.66	76.20
BX-IDC2.54-2-32PWZ	2*32	78.74	81.28



RECOMMEND P.C.B LAYOUT  
 PCB TOLERANCE: ±0.05 (TOP VIEW)

DRAWN	DESCRIPTION	DATE	GENERAL TOLERANCE		DRAWING	EMMA
			X.±0.30	X.*±5°		
			.X±0.20	.X*±1°	CHECK	EVA
			.XX±0.10	.XX*±0.5°	APPROVAL	JADE
					UNITS	MM SCALE 1:1

料號 PART NO.	BX-IDC2.54-2-NPWZ	版次 REV.	A
品名 TITLE	2.0DC3-nPin H5.7 90° PC2.8 PB9.3 L10.5/14.5 6T	頁數 SHEET	1/1
零件號 CUTM.NO.			
<b>Bossie (博錫)</b>			