









 PAD AREA
 KEEP OUT AREA
RECOMMENDED PCB LAYOUT
GENERAL TOLERANCE ± 0.05

SPECIFICATION
MATERIAL:
INSULATOR: HIGH TEMPERATURE THERMOPLASTIC, UL 94V-0.
CONTACT: C5210
SHELL: SUS
PLATING:
CONTACT: PLATED 50U" NI OVERALL CONTACT ALL AU 1U
SHELL: PLATED 50U" NI OVERALL, PAD AU 1U
ELECTRICAL:
CURRENT RATING: 0.5MA AC/DC MAX
VOLTAGE RATING: 125V AC/DC
AMBIENT TEMPERATURE RANGE: -40°C~+85°C
STORAGE TEMPERATURE RANGE: -40°C~+85°C
AMBIENT HUMIDITY RANGE: 95% R.H. MAX.
CONTACT RESISTANCE: 100MΩ MAX.
INSULATION RESISTANCE: 1000MΩ MIN./500VDC
REFLOW PEAK TEMP: 260°C ±5°C, 3~5 S
MATING CYCLES: 3,000 INSERTIONS MIN

NANO SIM CARD	
Pin No.	NAME
C1	VCC OF SIM
C2	RST OF SIM
C3	CLK OF SIM
C5	GND OF SIM
C6	VPP OF SIM
C7	I/O OF SIM
C4/C8	N/A


制圖 DRAWN	變更內容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制圖 DRAWING	EMMA			料號 PART NO.	BX-SMN-1.35HJ-C	版本 REV.	A
			X.±0.50	X.*±2"	審核 CHECK	EVA			品名 TITLE	NANO SIM CARD PUSH PULL 6PIN H1.35	頁數 SHEET	1/1
			.X±0.30	.X*±1"	核准 APPROVAL	JADE			客戶料號 CUTM.NO.			
			.XX±0.20	.XX*±0.5"								
					單位 UNITS	MM	比例 SCALE	1:1				






NOTES

1. NUMBER OF CONNECTORS: 1800PCS/REEL
2. LEAD TAPE LENGTH



3. QUANTITY: 18000PCS/CARTON



制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	EMMA	料号 PART NO.	BX-SMN-1.35HJ-C		版本 REV.	A
			X.±0.50	X.*±2°				品名 TITLE	NANO SIM CARD PUSH PULL 6PIN H1.35HJ-C		
			.X±0.30	.X*±1°	审核 CHECK	EVA	客户料号 CUTM.NO.			页次 SHEET	1/1
			.XX±0.20	.XX*±0.5°	批准 APPROVAL	JADE					
					单位 UNITS	MM	比例 SCALE	1:1			

Bossie (博锡)