


Part No	Pin	A	B	C
BX-HA2.54-2PLT	2	2.50	10.00	7.50
BX-HA2.54-3PLT	3	5.00	12.50	10.00
BX-HA2.54-4PLT	4	7.50	15.00	12.50
BX-HA2.54-5PLT	5	10.00	17.50	15.00
BX-HA2.54-6PLT	6	12.50	20.00	17.50
BX-HA2.54-7PLT	7	15.00	22.50	20.00
BX-HA2.54-8PLT	8	17.50	25.00	22.50
BX-HA2.54-9PLT	9	20.00	27.50	25.00
BX-HA2.54-10PLT	10	22.50	30.00	27.50
BX-HA2.54-11PLT	11	25.00	32.50	30.00
BX-HA2.54-12PLT	12	27.50	35.00	32.50
BX-HA2.54-13PLT	13	30.00	37.50	35.00
BX-HA2.54-14PLT	14	32.50	40.00	37.50
BX-HA2.54-15PLT	15	35.00	42.50	40.00
BX-HA2.54-16PLT	16	37.50	45.00	42.50

NOTES:

- 1.BASE: LCP
- 2.PIN: Brass
- 3.Solder Tab: Brass

SPECIFICATIONS:

- 1.Spacing: 2.5
- 2.Voltage Rating: 250V AC DC
- 3.Current Rating: 3A AC DC
- 4.Insulation Resistance: 800MΩ Min
- 5.Contact Resistance: 20mΩ Max
- 6.Withstanding voltage: 1000V AC 1/Minute
- 7.Temperatuer Range: -25℃ ~+ 85℃



制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	EMMA		料号 PART NO.	BX-HA2.54-NPLT		版本 REV.	A
			X.±0.20	X'.:±5°	审核 CHECK	EVA		品名 TITLE	WAFER HA2.54 立脚带扣		页次 SHEET	1/1
			.X±0.10	X.X':±3°	核准 APPROVAL	JADE		客户料号 CUTM.NO.				
			.XX±0.05	X.XX':±1°	单位 UNITS	MM	比例 SCALE	1:1	Bossie (博锡)			