






RoHS Compliant



NOTES:
 1.MATERIAL:
 HOUSING: HIGH TEMPERATURE THERMOPLASTIC UL94V_0,COLOR:BLACK.
 CONTACT: COPPER ALLOYS.
 2.PLATING:
 UNDERPLATE: 50u" NICKEL.
 CONTACT AREA: 1u" GOLD OVER 50u" NICKEL.
 3.MULTIMEDIA CARD COMPATIBLE



PIN NO.	DIM. A	DIM. B	DIM. C
28	17.50	13.50	14.57
29	18.00	14.00	15.07
30	18.50	14.50	15.57
31	19.00	15.00	16.07
32	19.50	15.50	16.57
33	20.00	16.00	17.07
34	20.50	16.50	17.57
35	21.00	17.00	18.07

PIN NO.	DIM. A	DIM. B	DIM. C
04	5.50	1.50	2.57
05	6.00	2.00	3.07
06	6.50	2.50	3.57
07	7.00	3.00	4.07
08	7.50	3.50	4.57
09	8.00	4.00	5.07
10	8.50	4.50	5.57
11	9.00	5.00	6.07
12	9.50	5.50	6.57
13	10.00	6.00	7.07
14	10.50	6.50	7.57
15	11.00	7.00	8.07
16	11.50	7.50	8.57
17	12.00	8.00	9.07
18	12.50	8.50	9.57
19	13.00	9.00	10.07
20	13.50	9.50	10.57
21	14.00	10.00	11.07
22	14.50	10.50	11.57
23	15.00	11.00	12.07
24	15.50	11.50	12.57
25	16.00	12.00	13.07
26	16.50	12.50	13.57
27	17.00	13.00	14.07
36	21.50	17.50	18.57
37	22.00	18.00	19.07
38	22.50	18.50	19.57
39	23.00	19.00	20.07
40	23.50	19.50	20.57
41	24.00	20.00	21.07
42	24.50	20.50	21.57
43	25.00	21.00	22.07
44	25.50	21.50	22.57
45	26.00	22.00	23.07
46	26.50	22.50	23.57
47	27.00	23.00	24.07
48	27.50	23.50	24.57
49	28.00	24.00	25.07
50	28.50	24.50	25.57
51	29.00	25.00	26.07
52	29.50	25.50	26.57
53	30.00	26.00	27.07
54	30.50	26.50	27.57
55	31.00	27.00	28.07
56	31.50	27.50	28.57
57	32.00	28.00	29.07
58	32.50	28.50	29.57
59	33.00	29.00	30.07
60	33.50	29.50	30.57

深圳市敏连达科技有限公司 Shenzhen Minlianda Technology Co.,Ltd.		品名 (ITEM NO)	0.5PH 2.0H 前插后压FPC		
		料号 (PART NO)	MLD-FPC-0.5RG-H20-XXP		
单位 (UNIT): MM	未注公差 TOLERANCE UNSPECIFIED	版次 (REV): A/O	页次 (PAGE): 1/1	设计 (DESIGN)	柯南
比例 (SCALE) 1:1	X.X ± 0.38 X.XX ± 0.20 X.XXX ± 0.10 X' ± 5' X.X' ± 2'	模号 (MODEL NO)		审核 (CHECKED)	邱敏
		图号 (DWG NO)	MLD-2509031032	核准 (APPROVED)	陈镇