



Part No	Pin	A	B	C
BX-XH2.54-2PWT	2	2.50	10.00	8.30
BX-XH2.54-3PWT	3	5.00	12.50	10.80
BX-XH2.54-4PWT	4	7.50	15.00	13.30
BX-XH2.54-5PWT	5	10.00	17.50	15.80
BX-XH2.54-6PWT	6	12.50	20.00	18.30
BX-XH2.54-7PWT	7	15.00	22.50	20.80
BX-XH2.54-8PWT	8	17.50	25.00	23.30
BX-XH2.54-9PWT	9	20.00	27.50	25.80
BX-XH2.54-10PWT	10	22.50	30.00	28.30
BX-XH2.54-11PWT	11	25.00	32.50	30.80
BX-XH2.54-12PWT	12	27.50	35.00	33.30
BX-XH2.54-13PWT	13	30.00	37.50	35.80
BX-XH2.54-14PWT	14	32.50	40.00	38.30
BX-XH2.54-15PWT	15	35.00	42.50	40.80
BX-XH2.54-16PWT	16	37.50	45.00	43.30

NOTES:

- 1.BASE: LCP
- 2.PIN: Brass
- 3.Solder Tab: Brass

SPECIFICATIONS:

- 1.Spacing: 2.5
- 2.Voltage Rating: 250V AC DC
- 3.Current Rating: 3A AC DC
- 4.Insulation Resistance: 800MΩ Min
- 5.Contact Resistance: 20mΩ Max
- 6.Withstanding voltage: 500V AC 1/Minute
- 7.Temperatuer Range: -25℃ ~+ 85℃

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	EMMA		料号 PART NO.	BX-XH2.54-NPWT		版本 REV.	A
			X.±0.20	X'.:±5°	审核 CHECK	EVA		品名 TITLE	WAFER 2.5 卧贴		页次 SHEET	1/1
			.X±0.10	X.X':±3°	核准 APPROVAL	JADE		客户料号 CUTM.NO.				
			.XX±0.05	X.XX':±1°	单位 UNITS	MM	比例 SCALE	1:1		Bossie (博锡)		