

RECOMMENDED PCB LAYOUT  
GENERAL TOLERANCE ±0.05

规格说明: Specifications:

电气特性: Electrical:

1. 额定电流: Current Rating  
1.5A/contact terminal
2. 额定电压: Voltage Rating  
30V DC
3. 接触阻抗: Contact Resistance  
30 milliohms MAX
4. 耐电压: Dielectric Withstanding Voltage:  
500 V AC AT Sea Level
5. 绝缘阻抗: Insulation Resistance:  
1000MEGA ohms MIN

物理性能: Mechanical:

1. 插拔力: Connector Mate and Unmate Force  
Mate force: 3.57kgf(MAX)  
Unmate force: 1.02kgf(MIN)
2. 端子保持力: Terminal Retention  
1.2kgf(MIN)

原材料: Material:

1. 塑胶: Housing:  
Hing Temperature Ternmaplastics,  
UI 94V-0 PBT White/Black
2. 端子: Contact: Copper Alloy C2680
3. 外壳: Shell: Copper Alloy C2680/SPCC

电镀: Finish:

1. 端子: Contact: Plated Gold in Mating Area;  
Tin On Solder Talls
2. 外壳: Shell:  
Nickel Plating



③	CONTACT	4	BRASS	GOLD FLASH/1u"/3u"/15u" T=0.25mm
②	HOUSING	1	PBT	WHITE
①	SHELL	1	SPCC	NICKE PLATING T=0.30mm
ITEM	PART NAME	Q'TY/PCS	MATERIALS	NOTE

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	EMMA	料号 PART NO.	BX-TYPE-A-MWC4P	版本 REV.	A										
			X.±0.30	X.*±5°							审核 CHECK	EVA	品名 TITLE	A/F 90度 DIP弯脚无边加盖	页次 SHEET	1/1				
			.X±0.20	.X*±2°													核准 APPROVAL	JADE	客户料号 CUTM.NO.	
			.XX±0.10																	
						<b>Bossie (博锡)</b>														





产品

10PCS/格



吸塑盒: 100PCS/盘




注释:

1. 吸塑盒: 140\*220\*17.5/CM


2. 吸塑盒材质: PET

3. 纸箱: 45\*29\*29/MM



3. 纸箱材质: K737K




放置地



纸箱: 5000PCS/箱



制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	料号 PART NO.	BX-TYPE-A-MWC4P	版本 REV.	A
			X.±0.30	X.*±5°	审核 CHECK	品名 TITLE	A/F 90度 DIP弯脚无边加盖	页次 SHEET	1/1
			.X±0.20	.X*±2°	核准 APPROVAL	客户料号 CUTM.NO.			
			.XX±0.10		单位 UNITS	MM		比例 SCALE	1:1
						<b>Bossie (博锡)</b>			