



Part No	Pin	A	B	C
BX-MX1.25-2PWT	2	1.25	7.50	
BX-MX1.25-3PWT	3	2.50	8.75	
BX-MX1.25-4PWT	4	3.75	10.00	2.50
BX-MX1.25-5PWT	5	5.00	11.25	3.75
BX-MX1.25-6PWT	6	6.25	12.50	5.00
BX-MX1.25-7PWT	7	7.50	13.75	6.25
BX-MX1.25-8PWT	8	8.75	15.00	7.50
BX-MX1.25-9PWT	9	10.00	16.25	8.75
BX-MX1.25-10PWT	10	11.25	17.50	10.00
BX-MX1.25-11PWT	11	12.50	18.75	11.25
BX-MX1.25-12PWT	12	13.75	20.00	12.50
BX-MX1.25-13PWT	13	15.00	21.25	13.75
BX-MX1.25-14PWT	14	16.25	22.50	15.00
BX-MX1.25-15PWT	15	17.50	23.75	16.25
BX-MX1.25-16PWT	16	18.75	25.00	17.50

NOTES:

- 1.BASE: LCP
- 2.PIN: Brass
- 3.Solder Tab: Brass

SPECIFICATIONS:

- 1.Spacing: 1.25
- 2.Voltage Rating: 125V AC DC
- 3.Current Rating: 1A AC DC
- 4.Insulation Resistance: 100MΩ Min
- 5.Contact Resistance: 20mΩ Max
- 6.Withstanding voltage: 500V AC 1/Minute
- 7.Temperatuer Range: -25℃ ~+ 85℃

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	EMMA		料号 PART NO.	BX-MX1.25-NPWT		版本 REV.	A
			X.±0.20	X'.:±5°	审核 CHECK	EVA		品名 TITLE	WAFER 1.25 晶圆		页次 SHEET	1/1
			.X±0.10	X.X':±3°	核准 APPROVAL	JADE		客户料号 CUTM.NO.				
			.XX±0.05	X.XX':±1°	单位 UNITS	MM	比例 SCALE	1:1				