



Part No	Pin	A	B	C
BX-ZH1.5-2PWT	2	1.50	6.00	3.65
BX-ZH1.5-3PWT	3	3.00	7.50	5.15
BX-ZH1.5-4PWT	4	4.50	9.00	6.65
BX-ZH1.5-5PWT	5	6.00	10.50	8.15
BX-ZH1.5-6PWT	6	7.50	12.00	9.65
BX-ZH1.5-7PWT	7	9.00	13.50	11.15
BX-ZH1.5-8PWT	8	10.50	15.00	12.65
BX-ZH1.5-9PWT	9	12.00	16.50	14.15
BX-ZH1.5-10PWT	10	13.50	18.00	15.65
BX-ZH1.5-11PWT	11	15.00	19.50	17.15
BX-ZH1.5-12PWT	12	16.50	21.00	18.65
BX-ZH1.5-13PWT	13	18.00	22.50	20.15
BX-ZH1.5-14PWT	14	19.50	24.00	21.65
BX-ZH1.5-15PWT	15	21.00	25.50	23.15
BX-ZH1.5-16PWT	16	22.50	27.00	24.65

NOTES:

- 1.BASE: LCP
- 2.PIN: Brass
- 3.Solder Tab: Brass

SPECIFICATIONS:

- 1.Spacing: 1.5
- 2.Voltage Rating: 250V AC DC
- 3.Current Rating: 1A AC DC
- 4.Insulation Resistance: 500MΩ Min
- 5.Contact Resistance: 20mΩ Max
- 6.Withstanding voltage: 500V AC 1/Minute
- 7.Temperatuer Range: -25℃ ~+ 85℃

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	EMMA		料号 PART NO.	BX-ZH1.5-NPWT		版本 REV.	A
			X.±0.20	X'.:±5°	审核 CHECK	EVA		品名 TITLE	WAFER 1.50 卧贴		页次 SHEET	1/1
			.X±0.10	X.X':±3°	核准 APPROVAL	JADE		客户料号 CUTM.NO.				
			.XX±0.05	X.XX':±1°	单位 UNITS	MM	比例 SCALE	1:1				