








▨ PAD AREA
■ KEEP OUT AREA

RECOMMENDED PCB LAYOUT
GENERAL TOLERANCE ± 0.05



MATERIAL:


INSULATOR: HIGH TEMPERATURE THERMOPLASTIC, UL 94V-0
CONTACT: COPPER ALLOY
SHELL: SUS

PLATING:

CONTACT: PLATED 50U" NI OVER ALL CONTACT AU 1U
SHELL: PLATED 50U" NI OVERALL
PLATED 1U" AU SELECTIVE CONTACT AREA

ELECTRICAL:


CURRENT RATING: 0.5MA
VOLTAGE RATING: 5V AC/DC
AMBIENT TEMPERATURE RANGE: $-40^{\circ}\text{C} \sim +85^{\circ}\text{C}$
STORAGE TEMPERATURE RANGE: $-40^{\circ}\text{C} \sim +85^{\circ}\text{C}$
AMBIENT HUMIDITY RANGE: 95% R.H. MAX.
CONTACT RESISTANCE: 100M MAX. Ω
INSULATION RESISTANCE: 1000M MIN./500VDC Ω
REFLOW PEAK TEMP: 260°C
MATING CYCLES: 5000MIN INSERTIONS
Salt spray time: 24H



MICRO SIM CARD	
Pin No.	NAME
C1	VCC OF SIM
C2	RST OF SIM
C3	CLK OF SIM
C5	GND OF SIM
C6	VPP OF SIM
C7	I/O OF SIM
C4/C8	N/A

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	EMMA	料号 PART NO.	BX-SIM-1.35H6PJ	版本 REV.	A
			X ± 0.15	X: $\pm 1^{\circ}$						
			.X ± 0.10		审核 CHECK	EVA	品名 TITLE	MICRO SIM CARD PUSH PUSH 6PIN H1.35	页次 SHEET	1/1
			.XX ± 0.05		批准 APPROVAL	JADE	客户料号 CUTM.NO.			
					单位 UNITS	MM	比例 SCALE	1:1		

Bossie (博锡)



NOTES

- 1.每卷包装数量:1000PCS/每卷
2.卷带包装方式:

空15PCS	产品1000PCS	空5PCS
轴心段空300mm	产品放置区	尾部100mm

- 3.每箱包装数量:10000PCS/箱
4.纸箱350mm*350mm*440mm(内部尺寸),材质K=K

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	EMMA	料号 PART NO.	BX-SIM-1.35H6PJ	版本 REV.	A
			X±0.15	X:±1°						
			.X±0.10							
			.XX±0.05							
					审核 CHECK	EVA	品名 TITLE	MICRO SIM CARD PUSH PUSH 6PIN H1.35 6Pin	页次 SHEET	1/1
					批准 APPROVAL	JADE	客户料号 CUTM.NO.			
					单位 UNITS	MM	比例 SCALE	1:1		