



技术指标:

1. 温度范围: $-25^{\circ}\text{C} \sim 85^{\circ}\text{C}$.
2. 额定电压: 250V AC, DC.
3. 耐压: 1500V AC/minute.
4. 接触电阻: $\leq 20\text{m}\Omega$.
5. 绝缘电阻: $\geq 1000\text{M}\Omega$.
6. 额定电流: 5A AC, DC.

材料:

1. 塑胶: PA66 米白色

型号	CKT	A	B
BX-5557-4.2-2-1P-MJK	2*1	0.00	5.50
BX-5557-4.2-2-2P-MJK	2*2	4.20	9.70
BX-5557-4.2-2-3P-MJK	2*3	8.40	13.90
BX-5557-4.2-2-4P-MJK	2*4	12.60	18.10
BX-5557-4.2-2-5P-MJK	2*5	16.80	22.30
BX-5557-4.2-2-6P-MJK	2*6	21.00	26.50
BX-5557-4.2-2-7P-MJK	2*7	25.20	30.70
BX-5557-4.2-2-8P-MJK	2*8	29.40	34.90
BX-5557-4.2-2-9P-MJK	2*9	33.40	39.10
BX-5557-4.2-2-10P-MJK	2*10	37.80	43.30
BX-5557-4.2-2-11P-MJK	2*11	42.00	47.50
BX-5557-4.2-2-12P-MJK	2*12	46.20	51.70

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	EMMA		料号 PART NO.	BX-5557-4.2-2-NP-MJK	版本 REV.	A
			X.±0.30	X.*±5°	审核 CHECK	EVA		品名 TITLE	WBM4.2MM HOUSING	页次 SHEET	1/1
			.X±0.25	.X*±1°	核准 APPROVAL	JADE		客户料号 CUTM.NO.			
			.XX±0.15		单位 UNITS	MM	比例 SCALE	1:1	 Bossie (博锡)		