





技术要求Specification:


1. 材质Material: PA66 UL94V-0:
2. 额定电流 Current rating:2.0A AC,DC
3. 额定电压 Voltage rating:250V AC,DC
4. 温度范围 Temperature range:-25℃to+85℃
5. 接触电阻 Contact resistance:≤20mΩ
6. 绝缘电阻Insulation resistance:≥1000MΩ
7. 耐压Withstand voltage:500V AC/minute
8. 塑件表面平整光洁,无明显的毛刺、气泡、变形、浇口拉伤、缺料等不良现象。
Plastic surface smooth and clean, no obvious glitches, bubbles, distortion, gate strain, lack of material and other undesirable phenomena.



此凸点只限10PIN以上的产品有,
2-10PIN均无此凸点



Part No	Pin	A	B	C	D	E
BX-HY2.0-2PJK	2	2.00	4.70	2.30	1.00	0.60
BX-HY2.0-3PJK	3	4.00	6.70	2.30	1.00	0.60
BX-HY2.0-4PJK	4	6.00	8.70	4.30	1.70	1.00
BX-HY2.0-5PJK	5	8.00	10.70	4.30	1.70	1.00
BX-HY2.0-6PJK	6	10.00	12.70	8.30	5.90	1.95
BX-HY2.0-7PJK	7	12.00	14.70	10.30	7.90	1.95
BX-HY2.0-8PJK	8	14.00	16.70	12.30	9.90	1.95
BX-HY2.0-9PJK	9	16.00	18.70	12.30	9.90	1.95
BX-HY2.0-10PJK	10	18.00	20.70	12.30	9.90	1.95
BX-HY2.0-11PJK	11	20.00	22.70	16.30	13.90	1.95
BX-HY2.0-12PJK	12	22.00	24.70	16.30	13.90	1.95
BX-HY2.0-13PJK	13	24.00	26.70	16.30	13.90	1.95
BX-HY2.0-14PJK	14	26.00	28.70	16.30	13.90	1.95
BX-HY2.0-15PJK	15	28.00	30.70	16.30	13.90	1.95
BX-HY2.0-16PJK	16	30.00	32.70	16.30	13.90	1.95



制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING
			X.±0.30	X.*±1°	
			.X±0.20		审核 CHECK
			.XX±0.10		核准 APPROVAL
					单位 UNITS

EMMA
EVA
JADE
MM
比例 SCALE
1:1

料号 PART NO.	BX-HY2.0-NPJK		版本 REV.	A
品名 TITLE	HY2.0MM HOUSING		页次 SHEET	1/1
客户料号 CUTM.NO.				

Bossie (博锡)