










RECOMMENDED P.C.B HOLE LAYOUT
COMPONENT SIDE VIEW(TOLERANCE: +/-0.05)

NOTES:

1. MATERIAL:

Housing: High Temperature Thermoplastic
UL94V-0; Color Black.

Contacts: Phosphor Bronze.

Tin 80u" at Solder Tail,

Selected Gold Flash on Contact Area plating.

Shell: Stainless.

Gold Flash on Contact solder Area

Over Nickel Plating.

2. Electrical Characteristics:

Operating voltage : 50v AC(rms)/DC.

Current rating : 0.5 A.

Operating Temperature: -40~+85℃

Insulation resistance: 1000M ohms min. at 500VDC

Dielectric withstanding voltage : 500 VAC/1minute.

Contact resistance: 100m ohms max.

3. Mechanical characteristics

Insertion force: 2.0kg Max.

Extraction force: 0.5kg Min.

Mating durability: 5000 cycles at the speed rate of
400-600 cycles/h; Without distortion of plastic and
serious wear and tear in terminal, No signal break.

TF CARD PIN DEFINE

PIN NO.	NAME	YTYPE	DESCRIPTION
1	DAT2	I/O/PP	DATE LINE(BIT2)
2	CD/DAT3	I/O/PP	CARD DETECT DATE LIN(BIT3)
3	CMD	PP	COMMAND RESPONSE
4	VDD	S	SUPPLY VOLTAGE
5	CLK	I	CLOCK
6	VSS	S	SUPPLY VOLTAGE GROUND
7	DAT0	I/O/PP	DATE LINE(BIT0)
8	DAT1	I/O/PP	DATE LINE(DIT1)
9	CARD DETECT		


开关插卡状态

CIRCUIT:		CD GROUND	
CD	GROUND	CD	GROUND
WITHOUT CARD	CARD INSERTED	WITHOUT CARD	CARD INSERTED

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	EMMA	
			X.±0.30	X.±2°	审核 CHECK	EVA	
			.X±0.20		批准 APPROVAL	JADE	
			.XX±0.10		单位 UNITS	MM	比例 SCALE
						1:1	

料号 PART NO.	品名 TITLE	客户料号 CUTM.NO.	版本 REV.	页次 SHEET
BX-TF-1.85HJ	T-FLASH CARD PUSH PUSH C TYPE 赫		A	1/1






NOTES

1. 每卷包装数量:1000PCS/每卷
2. 卷带包装方式:

空15PCS	产品1000PCS	空5PCS
轴心段空800mm	产品放置区	尾部400mm

3. 每箱包装数量: 10000PCS/箱



制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	EMMA	料号 PART NO.	BX-TF-1.85HJ	版本 REV.	A
			X.±0.30	X.±2°	审核 CHECK	EVA	品名 TITLE	T-FLASH CARD PUSH PUSH C TYPE 翻	页次 SHEET	1/1
			.X±0.20		核准 APPROVAL	JADE	客户料号 CUTM.NO.			
			.XX±0.10		单位 UNITS	MM	比例 SCALE	1:1	Bossie (博锡)	