



技术要求Specification:

- 1、材质Material: PA66 UL94V-0;
- 2、塑件表面平整光洁, 无明显的毛刺、气泡、变形、浇口拉伤、缺料等不良现象。

Plastic surface smooth and clean, no obvious burrs, bubbles, distortion, gate strain, lack of material and other undesirable phenomena.

| Part No        | Pin | A     | B     | C     |
|----------------|-----|-------|-------|-------|
| BX-SH1.0-2PJK  | 2   | 1.00  | 5.00  | 2.40  |
| BX-SH1.0-3PJK  | 3   | 2.00  | 6.00  | 3.40  |
| BX-SH1.0-4PJK  | 4   | 3.00  | 7.00  | 4.40  |
| BX-SH1.0-5PJK  | 5   | 4.00  | 8.00  | 5.40  |
| BX-SH1.0-6PJK  | 6   | 5.00  | 9.00  | 6.40  |
| BX-SH1.0-7PJK  | 7   | 6.00  | 10.00 | 7.40  |
| BX-SH1.0-8PJK  | 8   | 7.00  | 11.00 | 8.40  |
| BX-SH1.0-9PJK  | 9   | 8.00  | 12.00 | 9.40  |
| BX-SH1.0-10PJK | 10  | 9.00  | 13.00 | 10.40 |
| BX-SH1.0-11PJK | 11  | 10.00 | 14.00 | 11.40 |
| BX-SH1.0-12PJK | 12  | 11.00 | 15.00 | 12.40 |
| BX-SH1.0-13PJK | 13  | 12.00 | 16.00 | 13.40 |
| BX-SH1.0-14PJK | 14  | 13.00 | 17.00 | 14.40 |
| BX-SH1.0-15PJK | 15  | 14.00 | 18.00 | 15.40 |
| BX-SH1.0-16PJK | 16  | 15.00 | 19.00 | 16.40 |
| BX-SH1.0-17PJK | 17  | 16.00 | 20.00 | 17.40 |
| BX-SH1.0-18PJK | 18  | 17.00 | 21.00 | 18.40 |
| BX-SH1.0-19PJK | 19  | 18.00 | 22.00 | 19.40 |
| BX-SH1.0-20PJK | 20  | 19.00 | 23.00 | 20.40 |

| 制图<br>DRAWN | 变更内容<br>DESCRIPTION | 日期<br>DATE | GENERAL TOLERANCE |        | 制图<br>DRAWING  | EMMA |             | 料号<br>PART NO.   | BX-SH1.0-NPJK      |  | 版本<br>REV.  | A   |
|-------------|---------------------|------------|-------------------|--------|----------------|------|-------------|------------------|--------------------|--|-------------|-----|
|             |                     |            | X.±0.30           | X.*±1* | 审核<br>CHECK    | EVA  |             | 品名<br>TITLE      | SH1.0MM HOUSING    |  | 页次<br>SHEET | 1/1 |
|             |                     |            | .X±0.20           |        | 核准<br>APPROVAL | JADE |             | 客户料号<br>CUTM.NO. |                    |  |             |     |
|             |                     |            | .XX±0.10          |        | 单位<br>UNITS    | MM   | 比例<br>SCALE | 1:1              | <b>Bossie (博锡)</b> |  |             |     |