



规格说明: Specifications:

电气特性: Electrical:

1. 额定电流: Current Rating  
1.5A/contact terminal
2. 额定电压: Voltage Rating  
30V DC
3. 接触阻抗: Contact Resistance  
30 milliohms MAX
4. 耐压: Dielectric Withstanding Voltage:  
500 V AC AT Sea Level
5. 绝缘阻抗: Insulation Resistance:  
1000MEGA ohms MIN

物理性能: Mechanical:

1. 插拔力: Connector Mate and Unmate Force  
Mate force: 3.57kgf(MAX)  
Unmate force: 1.02kgf(MIN)
2. 端子保持力: Terminal Retention  
1.2kgf(MIN)

原材料: Material:

1. 塑胶: Housing:  
High Temperature Thermoplastics,  
UI 94V-0 PBT White
2. 端子: Contact: Copper Alloy C2680
3. 外壳: Shell: Copper Alloy C2680/SPCC

电镀: Finish:

1. 端子: Contact: Plated Gold in Mating Area;  
Tin On Solder Talls
2. 外壳: Shell:  
Nickel Plating

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	EMMA		料号 PART NO.	BX-TYPE-A-MCC4P	版本 REV.	A
			X.±0.30	X.*±5°	审核 CHECK	EVA		品名 TITLE	USB AF 2.0 侧插迷你USB 13.8高无壳	页次 SHEET	1/1
			.X±0.20	.X*±2°	核准 APPROVAL	JADE		客户料号 CUTM.NO.			
			.XX±0.10		单位 UNITS	MM	比例 SCALE	1:1	Bossie (博锡)		