










端子鍍半金鍍錫



▨ PAD AREA
 ■ KEEP OUT AREA
 RECOMMENDED PCB LAYOUT
 GENERAL TOLERANCE ±0.05



Circuit Diagram for Detect Switch






Specification:

- Electrical Characteristics:
 - Contact Current Rating: 0.5 Amperes.
 - Dielectric Withstanding Voltage: AC500V r.m.s.
 - Insulation Resistance: 1000 MΩ Minimum.
 - Contact Resistance: 40 mΩ Maximum.
- Environmental:
 - Operating Temperature: -25°C~+90°C.
- Environmental:
 - Mating Cycles: 5,000 Insertions.
- Mechanical Characteristics:
 - Card Push Insertion/Out Force: 0.2~1.40kgf.
 - Contact Separation Force: 0.20kgf Minimum.
- Material:
 - Insulator: HI-Temp Plastic UL 94V-0 Rated.
 - Contact: Copper Alloy(t=0.15mm).
 - Shell: Stainless Steel(t=0.15mm).
 - Spring: SWP.



PIN NO.	NAME	YTPE	DESCRIPTION
1	DAT2	I/O/PP	DATE LINE(BIT2)
2	CD/DAT3	I/O/PP	CARD DETECT DATE LIN(BIT3)
3	CMD	PP	COMMAND RESPONSE
4	VDD	S	SUPPLY VOLTAGE
5	CLX	I	CLOCK
6	VSS	S	SUPPLY VOLTAGE GROUND
7	DAT0	I/O/PP	DATE LINE(BIT0)
8	DAT1	I/O/PP	DATE LINE(DIT1)

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		审核 CHECK	EMMA	料号 PART NO.	BX-TF-1.8HX	版次 REV.	A
			X.±0.35	X.±3'						
			.X±0.25	.X±2'		EVA	品名 TITLE	MICRO SD CARD PUSH	页次 SHEET	1/1
			.XX±0.15			JADE	客户料号 CUTM.NO.			
					批准 APPROVAL					
					单位 UNITS	MM	比例 SCALE	1:1		






NO.2





NO.1



纸箱规格: 340*340*385

NO.4



NO.3

1. 材质要求:

- 1.1 纸箱的材质为K; 外形尺寸为34*34*38.5;
- 1.2 卷盘的材质为PS, 卷盘的外形尺寸为 $\phi 330*30.4$;
- 1.3 卷带的材质为PS, 卷带的外形尺寸为20200*24.00*3.0mm;

2. 包装方式:

- 2.1 将卷带放入包装机后, 前空5PCS, 后放产品1000PCS, 再后空5PCS; 上带留300MM长度。
- 2.2 将包装好的产品从包装机上取下并包装好, 贴上内盘标签;
- 2.3 把累叠好的12 盘叠放入纸箱中共计12Kset, 上下放纸板, 纸箱四个角塞护角纸;
- 2.4 把包装好的成品打包封箱, 并在纸箱外贴上标签

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	EMMA	料号 PART NO.	BX-TF-1.8HX	版本 REV.	页次 SHEET	A
			X.±0.35	X.'±3'							
			.X±0.25	.X'±2'	审核 CHECK	EVA	品名 TITLE	MICRO SD CARD PUSH PUSH SMT 不粘 精	1/1		
			.XX±0.15		批准 APPROVAL	JADE	客户料号 CUTM.NO.				
					单位 UNITS	MM	比例 SCALE	1:1			

