



技术要求Specification:

1. 材质Material: PA66 UL94V-2(0):
2. 额定电流 Current rating:3.0A AC,DC
3. 额定电压 Voltage rating:250V AC,DC
4. 温度范围 Temperature range:-25℃to+85℃
5. 接触电阻 Contact resistance:≤0.02Ω
6. 绝缘电阻Insulation resistance:≥1000MΩ
7. 耐压Withstand voltage:1000V AC/minute
8. 塑件表面平整光洁, 无明显的毛刺、气泡、变形、浇口拉伤、缺料等不良现象.

Plastic surface smooth and clean, no obvious glitches, bubbles, distortion, gate strain, lack of material and other undesirable phenomena.

Part No	Pin	A	B	C
BX-VH3.96-2PJK	2	3.96	8.20	3.55
BX-VH3.96-3PJK	3	7.92	12.10	7.40
BX-VH3.96-4PJK	4	11.88	16.06	7.40
BX-VH3.96-5PJK	5	15.84	20.02	7.40
BX-VH3.96-6PJK	6	19.80	23.98	7.40
BX-VH3.96-7PJK	7	23.76	27.94	7.40
BX-VH3.96-8PJK	8	27.72	31.90	7.40
BX-VH3.96-9PJK	9	31.68	35.86	7.40
BX-VH3.96-10PJK	10	35.64	39.82	7.40
BX-VH3.96-11PJK	11	39.60	43.78	7.40
BX-VH3.96-12PJK	12	43.56	47.74	7.40

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	EMMA	料号 PART NO.	BX-VH3.96-NPJK	版本 REV.	A
			X.±0.30	X.*±1*						
			.X±0.20		审核 CHECK	EVA	品名 TITLE	VH3.96MM HOUSING	页次 SHEET	1/1
			.XX±0.10		核准 APPROVAL	JADE	客户料号 CUTM.NO.			
					单位 UNITS	MM	比例 SCALE	1:1		