



Part No	Pin	A	B	C	D	E	F
BX-FPC05-1.5H6PX	6	7.1	2.5	3.6	3.5	2.5	2.5
BX-FPC05-1.5H8PX	8	8.1	3.5	4.6	4.5	3.5	3.5
BX-FPC05-1.5H10PX	10	9.1	4.5	5.6	5.5	4.5	4.5
BX-FPC05-1.5H12PX	12	10.1	5.5	6.6	6.5	5.5	5.5
BX-FPC05-1.5H14PX	14	11.1	6.5	7.6	7.5	6.5	6.5
BX-FPC05-1.5H16PX	16	12.1	7.5	8.6	8.5	7.5	7.5
BX-FPC05-1.5H20PX	20	14.1	9.5	10.6	10.5	9.5	9.5
BX-FPC05-1.5H24PX	24	16.1	11.5	12.6	12.5	11.5	11.5
BX-FPC05-1.5H26PX	26	17.1	12.5	13.6	13.5	12.5	12.5
BX-FPC05-1.5H28PX	28	18.1	13.5	14.6	14.5	13.5	13.5
BX-FPC05-1.5H30PX	30	19.1	14.5	15.6	15.5	14.5	14.5
BX-FPC05-1.5H40PX	40	24.1	19.5	20.6	20.5	19.5	19.5
BX-FPC05-1.5H50PX	50	29.1	24.5	25.6	25.5	24.5	24.5

NOTES: RECOMMENDED FPC/FFC DIMENSION

- 额定电流 Current rating: 0.5A
- 额定电压 Voltage rating: 50V
- 耐电压 Withstand voltage: 500V AC/minute
- 接触电阻 Contact resistance :≤40mΩ
- 绝缘电阻 Insulation resistance: 100MΩ MIN
- 工作温度 Working temperature: -25℃ ~ +85℃

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	EMMA	料号 PART NO.	BX-FPC05-1.5HNPX	版本 REV.	A
			X.±0.35	X.*±3°						
			.X±0.25	.X*±2°	审核 CHECK	EVA	品名 TITLE	FPC 0.5PH H1.5	前翻下接 SHEET	1/1
			.XX±0.15		核准 APPROVAL	JADE	客户料号 CUTM.NO.			
					单位 UNITS	MM	比例 SCALE	1:1		

