




Technical Index:
 1. Temperature range: -25°C~85°C.
 2. Rated voltage: 250V DC/AC(rms).
 3. Rated current: 7.0A.
 4. Contact resistance: ≤20mΩ.
 5. Withstanding voltage: 1500V AC/minute.
 6. Insulation resistance: ≥1000MΩ.



适用线路板(PCB LAYOUT)



Part No	Pin	A	B
BX-VH3.96-2PWZ-GW	2	3.96	7.92
BX-VH3.96-3PWZ-GW	3	7.92	11.88
BX-VH3.96-4PWZ-GW	4	11.88	15.84
BX-VH3.96-5PWZ-GW	5	15.84	19.80
BX-VH3.96-6PWZ-GW	6	19.80	23.76
BX-VH3.96-7PWZ-GW	7	23.76	27.72
BX-VH3.96-8PWZ-GW	8	27.72	31.68
BX-VH3.96-9PWZ-GW	9	31.68	35.64
BX-VH3.96-10PWZ-GW	10	35.64	39.60
BX-VH3.96-11PWZ-GW	11	39.60	43.56
BX-VH3.96-12PWZ-GW	12	43.56	47.52
BX-VH3.96-13PWZ-GW	13	47.52	51.48
BX-VH3.96-14PWZ-GW	14	51.48	55.44
BX-VH3.96-15PWZ-GW	15	55.44	59.40
BX-VH3.96-16PWZ-GW	16	59.40	63.36

序号	品名	材质	制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	EMMA	料号 PART NO.	BX-VH3.96-NPWZ-GW	版本 REV.	A
						X.±0.50	X'.:±5°						
1	VH3.96 胶芯	PA66 UL94V-2 Beige				.X±0.20	X.X':±3°	核准 APPROVAL	JADE	客户料号 CUTM.NO.			
2	VH3.96 弯针 端子	Copper Alloy/ Tin Plating				.XX±0.10	X.XX':±1°	单位 UNITS	MM	比例 SCALE	1:1		