



SPECIFICATIONS

- 1、Current Rating: 2A AC, DC
- 2、Voltage Rating: 100V AC, DC
- 3、Temperatuer Range: -25°C~ +85°C
- 4、Contact Resistance: 20mΩ Max
- 5、Insulation Resistance: 1000mΩ Min
- 6、Withstanding Voltang: 800V AC/minute
- 7、Material: Housing Nylon66 UL94-V0(2)

Circuit	Part NO.	Dimensions mm		
		A	B	C
2	FG-PH-2Y	2.00	5.80	4.60
3	FG-PH-3Y	4.00	7.80	6.60
4	FG-PH-4Y	6.00	9.80	8.60
5	FG-PH-5Y	8.00	11.80	10.60
6	FG-PH-6Y	10.00	13.80	12.60
7	FG-PH-7Y	12.00	15.80	14.60
8	FG-PH-8Y	14.00	17.80	16.60
9	FG-PH-9Y	16.00	19.80	18.60
10	FG-PH-10Y	18.00	21.80	20.60
11	FG-PH-11Y	20.00	23.80	22.60
12	FG-PH-12Y	22.00	25.80	24.60
13	FG-PH-13Y	24.00	27.80	26.60
14	FG-PH-14Y	26.00	29.80	28.60
15	FG-PH-15Y	28.00	31.80	30.60
16	FG-PH-16Y	30.00	33.80	32.60
18	FG-PH-18Y	34.00	37.80	36.60

			GENEAL TOLERANCE		制图 DRAWING		深圳市富港科技有限公司			
			DIM	TOL	审核 CHECK					
			X.X	±0.30	批准 APPROVAL		产品名称 TITLE	PH (2.00)单排 孔座	版本 REV.	A
1 初版发行			X.XX	±0.20	比例 SCALE		产品料号 PART NO.	FG-PH-NY	单位 UNITS	mm
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	X.XXX	±0.10	投影 Projection		材料 MATERIAL		页次 SHEET	1/1
			Angle	±3.0°						