





SECTION D-D  
2:1



SECTION C-C



SECTION A-A



SECTION B-B

技术要求Specification:

1. 材质:磷青,表面镀锡,

Material:Phos.Bronze Tin-Plated

镀层:Sn>2.50um, Ni>0.50um

2. 零件外观不得有有害毛刺、尖角、锐边和机械损伤;表面镀层应均匀、光亮、无雾斑、剥层等缺陷;

Parts may not have the appearance of harmful burrs,sharp corners,sharp edges and mechanical damage,surface coating should be uniform, bright,no fog spots,delamination and other defects.

3. 适用线号:AWG#32-#28

Wirerange: AWG#32-#28

3. 适用线号:AWG#32-#28:

Wirerange: AWG#32-#28

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	ROSE		料号 PART NO.	ZX-GH1.25-DZ	版本 REV.	A
			.X±0.20	X.*±1*	审核 CHECK	LEO		品名 TITLE	GH1.25MM TERMINAL	页次 SHEET	1/1
			.XX±0.15		核准 APPROVAL	JOHN		客户料号 CUTM.NO.			
			.XXX±0.10		单位 UNITS	MM	比例 SCALE	1:1	兆星精密电子(深圳)有限公司 ShenZhen ZhaoXing Precision electronics Co., Ltd.		