



Technical Index:

1. Temperature range:  $-40^{\circ}\text{C}\sim 105^{\circ}\text{C}$ .
2. Rated voltage: 200V DC/AC(rms).
3. Rated current: 2.0A.
4. Contact resistance:  $\leq 25\text{m}\Omega$ .
5. Withstanding voltage: 500V AC/minute.
6. Insulation resistance:  $\geq 1000\text{M}\Omega$ .

Part No	Pin	A	B
ZX-HY2.0-2PZZ-GW	2	2.00	6.00
ZX-HY2.0-3PZZ-GW	3	4.00	8.00
ZX-HY2.0-4PZZ-GW	4	6.00	10.00
ZX-HY2.0-5PZZ-GW	5	8.00	12.00
ZX-HY2.0-6PZZ-GW	6	10.00	14.00
ZX-HY2.0-7PZZ-GW	7	12.00	16.00
ZX-HY2.0-8PZZ-GW	8	14.00	18.00
ZX-HY2.0-9PZZ-GW	9	16.00	20.00
ZX-HY2.0-10PZZ-GW	10	18.00	22.00
ZX-HY2.0-11PZZ-GW	11	20.00	24.00
ZX-HY2.0-12PZZ-GW	12	22.00	26.00
ZX-HY2.0-13PZZ-GW	13	24.00	28.00
ZX-HY2.0-14PZZ-GW	14	26.00	30.00
ZX-HY2.0-15PZZ-GW	15	28.00	32.00
ZX-HY2.0-16PZZ-GW	16	30.00	34.00
ZX-HY2.0-17PZZ-GW	17	32.00	36.00
ZX-HY2.0-18PZZ-GW	18	34.00	38.00
ZX-HY2.0-19PZZ-GW	19	36.00	40.00
ZX-HY2.0-20PZZ-GW	20	38.00	42.00

序号	品名	材质	制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	ROSE	料号 PART NO.	ZX-HY2.0-NPZZ-GW	版本 REV.	A	
						.X±0.50	±2'							
1	HY2.0 直针 胶芯	PA66 UL94V-2 Beige				.XX±0.20		审核 CHECK	LEO	品名 TITLE	HY2.0 直针带扣	页次 SHEET	1/1	
2	HY2.0 直针 端子	Copper Alloy/ Tin Plating				.XXX±0.10		核准 APPROVAL	JOHN	客户料号 CUTM.NO.				
									单位 UNITS	MM	比例 SCALE	1:1	兆星精密电子(深圳)有限公司 ShenZhen ZhaoXing Precision electronics Co., Ltd.	