





SPECIFICATIONS

- 1、Current Rating: 3A AC, DC
- 2、Voltage Rating: 250V AC, DC
- 3、Temperatuer Range: -25℃~ +85℃
- 4、Contact Resistance: 20mΩ Max
- 5、Insulation Resistance: 1000mΩ Min
- 6、Withstanding Voltang: 1000V AC/minute
- 7、Material: Housing Nylon66 UL94-V0(2)



Circuit	Part NO.	Dimensions mm				
		A	B	C	D	E
2	FG-XHB-2Y	2.50	7.00	5.70	5.30	2.50
3	FG-XHB-3Y	5.00	9.50	8.20	5.10	3.10
4	FG-XHB-4Y	7.50	12.00	10.70	5.10	2.20
5	FG-XHB-5Y	10.00	14.50	13.20	7.60	4.70
6	FG-XHB-6Y	12.50	17.00	15.70	10.10	7.20
7	FG-XHB-7Y	15.00	19.50	18.20	12.60	9.70
8	FG-XHB-8Y	17.50	22.00	20.70	15.10	12.20
9	FG-XHB-9Y	20.00	24.50	23.20	17.60	14.70
10	FG-XHB-10Y	22.50	27.00	25.70	15.10	12.20
11	FG-XHB-11Y	25.00	29.50	28.20	15.10	12.20
12	FG-XHB-12Y	27.50	32.00	30.70	15.10	12.20
13	FG-XHB-13Y	30.00	34.50	33.20	15.10	12.20
14	FG-XHB-14Y	32.50	37.00	35.70	15.10	12.20
15	FG-XHB-15Y	35.00	39.50	38.20	15.10	12.20



			GENREL TOLERANCE		制 图 DRAWING		深圳市富港科技有限公司			
			DIM	TOL	审 核 CHECK					
			X. X	±0.30	批 准 APPROVAL		产品名称 TITLE	XHB (2.50) 孔座	版本 REV.	A
1			初版发行		比 例 SCALE		产品料号 PART NO.	FG-XHB-NY	单 位 UNITS	mm
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	Angle ±3.0°		投 影 Projection		材 料 MATERIAL		页 次 SHEET	1/1