



技术要求Specification:

1. 材质Material: PA66 UL94V-0:
2. 额定电流 Current rating:1.0A AC,DC
3. 额定电压 Voltage rating:50V AC,DC
4. 温度范围 Temperature range:-25℃to+85℃
5. 接触电阻 Contact resistance:≤20mΩ
6. 绝缘电阻Insulation resistance:≥100MΩ
7. 耐压Withstand voltage:250V AC/minute
8. 塑件表面平整光洁, 无明显的毛刺、气泡、变形、浇口拉伤、缺料等不良现象。

Plastic surface smooth and clean, no obvious burrsbubbles, distortion, gate strain, lack of material and otherundesirable phenomena.

| Part No         | Pin | A     | B     | C     |
|-----------------|-----|-------|-------|-------|
| ZX-MX1.25-2PJK  | 2   | 1.25  | 4.30  | 3.00  |
| ZX-MX1.25-3PJK  | 3   | 2.50  | 5.55  | 4.25  |
| ZX-MX1.25-4PJK  | 4   | 3.75  | 6.80  | 5.50  |
| ZX-MX1.25-5PJK  | 5   | 5.00  | 8.05  | 6.75  |
| ZX-MX1.25-6PJK  | 6   | 6.25  | 9.30  | 8.00  |
| ZX-MX1.25-7PJK  | 7   | 7.50  | 10.55 | 9.25  |
| ZX-MX1.25-8PJK  | 8   | 8.75  | 11.80 | 10.50 |
| ZX-MX1.25-9PJK  | 9   | 10.00 | 13.05 | 11.75 |
| ZX-MX1.25-10PJK | 10  | 11.25 | 14.30 | 13.00 |
| ZX-MX1.25-11PJK | 11  | 12.50 | 15.55 | 14.25 |
| ZX-MX1.25-12PJK | 12  | 13.75 | 16.80 | 15.50 |
| ZX-MX1.25-13PJK | 13  | 15.00 | 18.05 | 16.75 |
| ZX-MX1.25-14PJK | 14  | 16.25 | 19.30 | 18.00 |
| ZX-MX1.25-15PJK | 15  | 17.50 | 20.55 | 19.25 |
| ZX-MX1.25-16PJK | 16  | 18.75 | 21.80 | 20.50 |

|             |                     |            |                   |        |               |                  |                |   |            |   |             |     |             |                  |             |     |                |      |
|-------------|---------------------|------------|-------------------|--------|---------------|------------------|----------------|---|------------|---|-------------|-----|-------------|------------------|-------------|-----|----------------|------|
| 制图<br>DRAWN | 变更内容<br>DESCRIPTION | 日期<br>DATE | GENERAL TOLERANCE |        | 制图<br>DRAWING | ROSE             | 料号<br>PART NO. | ZX-MX1.25-NPJK  | 版本<br>REV. | A |             |     |             |                  |             |     |                |      |
|             |                     |            | .X±0.30           | X.*±1* |               |                  |                |   |            |   | 审核<br>CHECK | LEO | 品名<br>TITLE | MX1.25MM HOUSING | 页次<br>SHEET | 1/1 |                |      |
|             |                     |            | .XX±0.20          |        |               |                  |                |   |            |   |             |     |             |                  |             |     | 核准<br>APPROVAL | JOHN |
|             |                     |            | .XXX±0.10         |        |               |                  |                |   |            |   |             |     |             |                  |             |     |                |      |
|             |                     |            |                   |        |               | 客户料号<br>CUTM.NO. |                | 兆星精密电子(深圳)有限公司<br>ShenZhen ZhaoXing Precision electronics Co., Ltd. |            |   |             |     |             |                  |             |     |                |      |