



Part No	Pin	A	B	C
ZX-XH2.54-2PLT	2	2.50	10.00	7.50
ZX-XH2.54-3PLT	3	5.00	12.50	10.00
ZX-XH2.54-4PLT	4	7.50	15.00	12.50
ZX-XH2.54-5PLT	5	10.00	17.50	15.00
ZX-XH2.54-6PLT	6	12.50	20.00	17.50
ZX-XH2.54-7PLT	7	15.00	22.50	20.00
ZX-XH2.54-8PLT	8	17.50	25.00	22.50
ZX-XH2.54-9PLT	9	20.00	27.50	25.00
ZX-XH2.54-10PLT	10	22.50	30.00	27.50
ZX-XH2.54-11PLT	11	25.00	32.50	30.00
ZX-XH2.54-12PLT	12	27.50	35.00	32.50
ZX-XH2.54-13PLT	13	30.00	37.50	35.00
ZX-XH2.54-14PLT	14	32.50	40.00	37.50
ZX-XH2.54-15PLT	15	35.00	42.50	40.00
ZX-XH2.54-16PLT	16	37.50	45.00	42.50

NOTES:
 1.BASE: LCP
 2.PIN: Brass
 3.Solder Tab: Brass

SPECIFICATIONS:
 1.Spacing: 2.5
 2.Voltage Rating: 250V AC DC
 3.Current Rating: 3A AC DC
 4.Insulation Resistance: 800MΩ Min
 5.Contact Resistance: 20mΩ Max
 6.Withstanding voltage: 1000V AC 1/Minute
 7.Temperatuer Range: -25℃ ~+ 85℃

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE	
			.X±0.20	X°.±5°
			.XX±0.10	X.X°.±3°
			.XXX±0.05	X.XX°.±1°

制图 DRAWING	ROSE
审核 CHECK	LEO
核准 APPROVAL	JOHN
单位 UNITS	MM
比例 SCALE	1:1

料号 PART NO.	ZX-XH2.54-NPLT	版本 REV.	A
品名 TITLE	WAFER 2.54 立贴	页次 SHEET	1/1
客户料号 CUTM.NO.			
 兆星精密电子 (深圳) 有限公司 ShenZhen ZhaoXing Precision electronics Co., Ltd.			